


ME MAX 45 MT CL 2-2 BU - Intermediate element



2200633

<https://www.phoenixcontact.com/us/products/2200633>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, Intermediate element, tall design, with vents, width: 22.6 mm, height: 99 mm, depth: 112.85 mm, color: blue (similar RAL 5015)

Your advantages

- Easy installation
- Variety of connection technology
- Can be mounted on the DIN rail

Commercial data

Item number	2200633
Packing unit	50 pc
Minimum order quantity	250 pc
Note	Made to order (non-returnable)
Product key	ACHABZ
GTIN	4046356641166
Weight per piece (including packing)	25.92 g
Weight per piece (excluding packing)	18.7 g
Country of origin	DE

ME MAX 45 MT CL 2-2 BU - Intermediate element



2200633

<https://www.phoenixcontact.com/us/products/2200633>

Technical data

Notes

Assembly note	Please observe the application note in the download area.
---------------	---

Product properties

Product type	Complete housing center part
Housing type	DIN rail housing
Housing series	ME-MAX
Product family	ME MAX.. 2-2
Number of rows	2
Ventilation openings present	yes

Dimensions

Dimensional drawing	
Width	22.6 mm
Height	99 mm
Depth	112.85 mm
Depth from top edge of DIN rail	107 mm

Material specifications

Color	blue (RAL 5015)
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600
Housing material	PA

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

PCB data

Type of PCB mount	Latching
-------------------	----------

ME MAX 45 MT CL 2-2 BU - Intermediate element



2200633


<https://www.phoenixcontact.com/us/products/2200633>

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

Drawings

Dimensional drawing



Schematic figure for illustrating the item dimensions. The figure is not of the desired product. For further details, refer to the product drawings in the "Downloads" tab.

ME MAX 45 MT CL 2-2 BU - Intermediate element



2200633

<https://www.phoenixcontact.com/us/products/2200633>

Classifications

UNSPSC

UNSPSC 21.0	31261501
-------------	----------

ME MAX 45 MT CL 2-2 BU - Intermediate element



2200633

<https://www.phoenixcontact.com/us/products/2200633>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com