

RPI-BC A+-ADAPTER ATGY - Adapter



2202906

<https://www.phoenixcontact.com/us/products/2202906>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Optional adapter for RPI-BC housing for using the Raspberry Pi A+



Your advantages

- Tool-free mounting
- Plenty of space for additional circuits on matrix or additional boards
- GPIO strip can be used with PTSM series connection technology
- Easy module-to-module connection, thanks to bus connection via DIN rails

Commercial data

Item number	2202906
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC10
Product key	ACHBAE
GTIN	4055626257235
Weight per piece (including packing)	5.2 g
Weight per piece (excluding packing)	2.22 g
Customs tariff number	85472000
Country of origin	DE

RPI-BC A+-ADAPTER ATGY - Adapter



2202906

<https://www.phoenixcontact.com/us/products/2202906>

Technical data

Product properties

Product type	Adapter
Housing type	DIN rail housing for use in distribution boards in accordance with DIN 43880
Housing series	BC
Ventilation openings present	no

Dimensions

Width	57.6 mm
Height	21.9 mm
Depth	17 mm

Material specifications

Color (Housing)	anthracite grey (RAL 7016)
Material Housing	PA
Flammability rating according to UL 94	V0
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

RPI-BC A+-ADAPTER ATGY - Adapter



2202906

<https://www.phoenixcontact.com/us/products/2202906>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2202906>



UL Recognized

Approval ID: E240868

RPI-BC A+-ADAPTER ATGY - Adapter



2202906

<https://www.phoenixcontact.com/us/products/2202906>

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

RPI-BC A+-ADAPTER ATGY - Adapter



2202906
<https://www.phoenixcontact.com/us/products/2202906>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com