

FLKM 24-PA/SO416 - System connectors



2293792

<https://www.phoenixcontact.com/us/products/2293792>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Commercial data

Item number	2293792
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C429
Product key	DK2BMG
GTIN	4017918365189
Weight per piece (including packing)	42.4 g
Weight per piece (excluding packing)	42.4 g
Customs tariff number	85366990
Country of origin	US

FLKM 24-PA/SO416 - System connectors



2293792

<https://www.phoenixcontact.com/us/products/2293792>

Technical data

Product properties

Product type	Front adapter
--------------	---------------

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

Trade restriction

CE note	The products are offered exclusively for export outside the EU and the European Economic Area.
---------	--

FLKM 24-PA/SO416 - System connectors



2293792

<https://www.phoenixcontact.com/us/products/2293792>

Classifications

ECLASS

ECLASS-13.0	27242292
ECLASS-15.0	27242292

ETIM

ETIM 8.0	EC002584
----------	----------

UNSPSC

UNSPSC 21.0	32151601
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, Not qualified for the European market
---	---

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------