

# PSD-S OE LED FL BU - Optical element



2700134

<https://www.phoenixcontact.com/us/products/2700134>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



LED flashing beacon element, 24 V DC, double lightning, blue

## Your advantages

- Tool-free element changeover
- High light and color intensity
- Can be freely combined
- Minimum LED service life of 50,000 h
- Optimum detection thanks to double flash
- Degree of protection IP65

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2700134       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | DR07          |
| Product key                          | DRL112        |
| GTIN                                 | 4046356491266 |
| Weight per piece (including packing) | 87.9 g        |
| Weight per piece (excluding packing) | 71 g          |
| Customs tariff number                | 85318070      |
| Country of origin                    | DE            |

## Technical data

### Notes

#### Note on application

|                     |                         |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

### Product properties

|                     |                |
|---------------------|----------------|
| Product type        | Signal element |
| Product family      | PSD-S          |
| Area of application | Signal tower   |

### Electrical properties

#### General

|                         |                                       |
|-------------------------|---------------------------------------|
| Input voltage           | 24 V DC                               |
| Maximum inrush current  | max. 200 mA                           |
| Current consumption     | typ. 35 mA                            |
| Source of light type    | LED                                   |
| Operating time          | 100 %                                 |
| Service life electrical | max. 50,000 h                         |
| Optical signal type     | LED flashing beacon with double flash |
| Signal frequency        | approx. 1 Hz                          |

### Dimensions

|          |         |
|----------|---------|
| Height   | 65.5 mm |
| Diameter | 70 mm   |

### Material specifications

|               |                  |
|---------------|------------------|
| Calotte color | blue             |
| Material      | Polycarbonate PC |

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                                         |
|---------------------------------|-----------------------------------------|
| Degree of protection            | IP65 (when installed or with end cover) |
| Ambient temperature (operation) | -20 °C ... 50 °C                        |

### Mounting

|                   |                                                        |
|-------------------|--------------------------------------------------------|
| Mounting type     | Plug-in mounting (Seal pre-installed for each element) |
| Mounting position | any                                                    |

# PSD-S OE LED FL BU - Optical element



2700134

<https://www.phoenixcontact.com/us/products/2700134>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2700134>



**cULus Listed**

Approval ID: E123528

# PSD-S OE LED FL BU - Optical element



2700134

<https://www.phoenixcontact.com/us/products/2700134>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27371220 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000232 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 46171600 |
|-------------|----------|

## Environmental product compliance

### EU RoHS

|                                         |              |
|-----------------------------------------|--------------|
| Fulfills EU RoHS substance requirements | Yes          |
| Exemption                               | 7(a), 7(c)-I |

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 801a28b6-d9bf-4602-94e4-f81477c5cf3c |