

SD FLASH 2GB APPLIC A M-W - Program/configuration memory



2701976

<https://www.phoenixcontact.com/us/products/2701976>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Program and configuration memory for extending the internal Flash memory, plug-in, 2 GB with license key for basic function block libraries for the marine and wind power industry.

Your advantages

- Program and configuration memory, plug-in, with license key for function block libraries
- License key for the function block libraries
- For storing application programs and other files in the file system of the PLC

Commercial data

Item number	2701976
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRAAZA
GTIN	4046356901321
Weight per piece (including packing)	9.2 g
Weight per piece (excluding packing)	8.5 g
Country of origin	DE

SD FLASH 2GB APPLIC A M-W - Program/configuration memory



2701976

<https://www.phoenixcontact.com/us/products/2701976>

Technical data

Product properties

Product type	Storage medium
Application	Marine and wind power industry
Mounting position	vertical

Electrical properties

Maximum power dissipation for nominal condition	0.165 W
---	---------

Supply

Supply voltage	3.3 V DC
Supply voltage range	2.7 V DC ... 3.6 V DC
Typical current consumption	typ. 50 mA

Material specifications

Housing material	Plastic
------------------	---------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

Mounting

Mounting position	vertical
-------------------	----------

SD FLASH 2GB APPLIC A M-W - Program/configuration memory



2701976

<https://www.phoenixcontact.com/us/products/2701976>

Classifications

UNSPSC

UNSPSC 21.0	32101606
-------------	----------

SD FLASH 2GB APPLIC A M-W - Program/configuration memory



2701976

<https://www.phoenixcontact.com/us/products/2701976>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com