

RAD-CONF-RF5 - Configuration memory



2902815
<https://www.phoenixcontact.com/us/products/2902815>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Radioline - configuration stick for easy and safe network addressing for the 2.4 GHz wireless module (RAD-2400-...), unique network ID, RF band 5

Your advantages

- Easy, unique, and safe network addressing
- Parallel operation of multiple networks (using different RF bands)

Commercial data

Item number	2902815
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN23
Product key	DNC61Z
GTIN	4046356682107
Weight per piece (including packing)	5.5 g
Weight per piece (excluding packing)	5.5 g
Customs tariff number	85235110
Country of origin	DE

RAD-CONF-RF5 - Configuration memory



2902815

<https://www.phoenixcontact.com/us/products/2902815>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Storage medium
--------------	----------------

RAD-CONF-RF5 - Configuration memory


2902815

<https://www.phoenixcontact.com/us/products/2902815>



Drawings

Schematic diagram



Configuration via CONFSTICK

RAD-CONF-RF5 - Configuration memory



2902815

<https://www.phoenixcontact.com/us/products/2902815>

Classifications

ECLASS

ECLASS-13.0	27242212
ECLASS-15.0	27242212

ETIM

ETIM 9.0	EC000192
----------	----------

UNSPSC

UNSPSC 21.0	32101600
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%