

VIP/S/BASE 3L DIVIDER - Partition plate



2907715

<https://www.phoenixcontact.com/us/products/2907715>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

VIP I/O marshalling partition plate for safe isolation between non-Ex i and Ex i plug-in modules on a base module in VIP design.
The partition plate is mounted directly on the base module between the plug-in IOAs.



Your advantages

- Snap-on connection to VIP base module
- Durable, sleek design

Commercial data

Item number	2907715
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C480
Product key	DK115Z
GTIN	4055626254883
Weight per piece (including packing)	6.5 g
Weight per piece (excluding packing)	6.5 g
Customs tariff number	85389099
Country of origin	US

VIP/S/BASE 3L DIVIDER - Partition plate



2907715

<https://www.phoenixcontact.com/us/products/2907715>

Technical data

Product properties

Product type	Partition plate
Product family	VIP I/O-Marshalling

Material specifications

Color	gray (RAL 7042)
Material	PA 6.6
Flammability rating according to UL 94	V0

Dimensions

Width	5.1 mm
Height	56.9 mm
Depth	91 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 75 °C
Permissible humidity (operation)	0 % ... 95 % (non-condensing)

VIP/S/BASE 3L DIVIDER - Partition plate



2907715

<https://www.phoenixcontact.com/us/products/2907715>

Classifications

ECLASS

ECLASS-13.0	27371392
ECLASS-15.0	27371392

ETIM

ETIM 9.0	EC002498
----------	----------

UNSPSC

UNSPSC 21.0	39121100
-------------	----------

VIP/S/BASE 3L DIVIDER - Partition plate



2907715

<https://www.phoenixcontact.com/us/products/2907715>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com