

# UPS-BAT-KIT-VRLA 2X12V/38AH - Uninterruptible power supply replacement battery



2908237  
<https://www.phoenixcontact.com/us/products/2908237>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Replacement battery for UPS-BAT/VRLA... battery modules



## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2908237       |
| Packing unit                         | 1 pc          |
| Sales key                            | CM24          |
| Product key                          | CMUEV3        |
| GTIN                                 | 4055626297750 |
| Weight per piece (including packing) | 25,500 g      |
| Weight per piece (excluding packing) | 25,200 g      |
| Customs tariff number                | 85072080      |
| Country of origin                    | CN            |

# UPS-BAT-KIT-VRLA 2X12V/38AH - Uninterruptible power supply replacement battery



2908237

<https://www.phoenixcontact.com/us/products/2908237>

## Technical data

### Input data

|               |            |
|---------------|------------|
| Input voltage | 2x 12 V DC |
|---------------|------------|

### Energy storage

|                                       |                                          |
|---------------------------------------|------------------------------------------|
| Nominal capacity                      | 38 Ah                                    |
| Battery module service life           | 10 Years ... 12 Years (20 °C)            |
| Latest startup date (battery only)    | 12 Months (0 °C ... 20 °C)               |
| Latest startup (battery only) - range | 9 Months ... 12 Months (20 °C ... 30 °C) |
|                                       | 6 Months ... 9 Months (30 °C ... 40 °C)  |
| Battery technology                    | VRLA-AGM                                 |
| Accumulator type                      | Panasonic LC-P1238APG                    |
| IQ technology                         | no                                       |

### Product properties

|                |                     |
|----------------|---------------------|
| Product type   | Battery             |
| Product family | Replacement battery |
| IQ technology  | no                  |

### Dimensions

|        |        |
|--------|--------|
| Width  | 330 mm |
| Height | 175 mm |
| Depth  | 175 mm |

### Environmental and real-life conditions

#### Ambient conditions

|                                                |                |
|------------------------------------------------|----------------|
| Ambient temperature (operation)                | 0 °C ... 40 °C |
| Ambient temperature (storage/transport)        | 0 °C ... 40 °C |
| Max. permissible relative humidity (operation) | ≤ 95 %         |

# UPS-BAT-KIT-VRLA 2X12V/38AH - Uninterruptible power supply replacement battery



2908237  
<https://www.phoenixcontact.com/us/products/2908237>

## Classifications

### ETIM

|          |          |
|----------|----------|
| ETIM 8.0 | EC011878 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26111700 |
|-------------|----------|

# UPS-BAT-KIT-VRLA 2X12V/38AH - Uninterruptible power supply replacement battery



2908237

<https://www.phoenixcontact.com/us/products/2908237>

## Environmental product compliance

### EU RoHS

|                                         |                                                                                     |
|-----------------------------------------|-------------------------------------------------------------------------------------|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|-----------------------------------------|-------------------------------------------------------------------------------------|

### China RoHS

|                                        |                                                                                                                                                                                                                                             |
|----------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-6<br>An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |
|----------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)