

EMG150-H 52MM GN - Covering hood



2943521

<https://www.phoenixcontact.com/us/products/2943521>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Covering hood, for the contact and dust-protected encapsulation of the components, in green design. Height: 52 mm, width: 150 mm

Commercial data

Item number	2943521
Packing unit	5 pc
Minimum order quantity	5 pc
Note	Made to order (non-returnable)
Sales key	AC11
Product key	ACHCBA
GTIN	4017918081133
Weight per piece (including packing)	66.44 g
Weight per piece (excluding packing)	66.44 g
Customs tariff number	85369010
Country of origin	DE

EMG150-H 52MM GN - Covering hood



2943521

<https://www.phoenixcontact.com/us/products/2943521>

Technical data

Product properties

Product type	Upper housing part
Housing type	Component housing
Number of positions	58

Dimensions

Width	150 mm
Installed height	52 mm
Depth	75 mm
Length	38 mm

Material specifications

Color	green
Flammability rating according to UL 94	V0
Housing material	Polycarbonate fiber reinforced PC-F

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 125 °C

Mounting

Mounting type	Snap in
---------------	---------

EMG150-H 52MM GN - Covering hood



2943521
<https://www.phoenixcontact.com/us/products/2943521>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com