

VISU+ 2 RT 512 WEB1 NETWORK - Visualization software



2988081

<https://www.phoenixcontact.com/us/products/2988081>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Runtime license for Visu+ including 1 web client and networking function where the I/O data and variables in scripting are limited to 512 bytes.

Your advantages

- Access protection with user management
- Fully scalable process diagrams for using one design on different devices and monitor sizes
- Multilingual software and projects, thanks to Unicode support and online selection
- Full SCADA (Supervisory Control And Data Acquisition) function with visualization, trend representation, and alarm management
- Data logging, trend display, and recipe management
- Scripts can be created in VBA and IL
- Control coupling with OPC

Commercial data

Item number	2988081
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR13
Product key	DRDAAB
GTIN	4046356566452
Weight per piece (including packing)	22 g
Weight per piece (excluding packing)	20 g
Customs tariff number	49119900
Country of origin	DE

VISU+ 2 RT 512 WEB1 NETWORK - Visualization software



2988081

<https://www.phoenixcontact.com/us/products/2988081>

Technical data

Product properties

Product type	Visualization
Basic functions	Know-How protection and safety through encoding of projects
	Realtime database coupling with ODBC to MS ACCESS, MS EXCEL and SQL server
	FDA CFR 21 Part 11 compatible
Expanded functionality	Web client capability
	Networking

System properties

Intended use for the software	Visualization
-------------------------------	---------------

License information

Type of license	Runtime license
-----------------	-----------------

Functionality

Basic functions	Know-How protection and safety through encoding of projects
	Realtime database coupling with ODBC to MS ACCESS, MS EXCEL and SQL server
	FDA CFR 21 Part 11 compatible
Expanded functionality	Web client capability
	Networking
Integrated function	Online configuration
	Password protection
	Language selection
	Networking
	Web client
Number of I/O nodes	512
Number of clients	1

System requirements

Hard disk memory	min. 1 GByte (recommended: 2 GB)
Supported browsers	Internet Explorer 5.5 or higher
Languages supported	German, English, French, Italian
Optical drive	DVD-ROM
Screen resolution	1024 x 768 pixel(s) (XGA)

System requirements for development environment

Operating equipment	Keyboard, mouse
Operating system	Windows® 11
	Windows® 10
	Windows® 8.1
	Windows® 8
	Windows® 7

VISU+ 2 RT 512 WEB1 NETWORK - Visualization software



2988081

<https://www.phoenixcontact.com/us/products/2988081>

	Windows® Embedded Standard 7
	Windows® Server 2019
	Windows® Server 2016
	Windows® Server 2012 R2
	Windows® Server 2012
	Windows® Server 2008 R2
	Windows® Server 2008
	Windows® Server 2003

System requirements for runtime environment

Operating system	Windows® 11
	Windows® 10
	Windows® 8.1
	Windows® 8
	Windows® 7
	Windows® Embedded Standard 7
	Windows® XP Embedded
	Windows® Server 2019
	Windows® Server 2016
	Windows® Server 2012 R2
	Windows® Server 2012
	Windows® Server 2008 R2
	Windows® Server 2008
	Windows® Server 2003
	Windows® CE 5.0
	Windows® CE 6.0
	Windows® Mobile

VISU+ 2 RT 512 WEB1 NETWORK - Visualization software



2988081
<https://www.phoenixcontact.com/us/products/2988081>

Classifications

ECLASS

ECLASS-13.0	27242502
-------------	----------

ETIM

ETIM 9.0	EC001416
----------	----------

UNSPSC

UNSPSC 21.0	43231500
-------------	----------

VISU+ 2 RT 512 WEB1 NETWORK - Visualization software



2988081
<https://www.phoenixcontact.com/us/products/2988081>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com