

SB 3-8-T O. SCHR. - Bridge bar

3026845

<https://www.phoenixcontact.com/us/products/3026845>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Bridge bar, number of positions: 3, color: orange



Commercial data

Item number	3026845
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Product key	BE1Z2X
GTIN	4017918193935
Weight per piece (including packing)	3.48 g
Weight per piece (excluding packing)	3.48 g
Country of origin	PL

SB 3-8-T O. SCHR. - Bridge bar

3026845

<https://www.phoenixcontact.com/us/products/3026845>



Technical data

Product properties

Product type	Bridge bar
Number of positions	3
Potentials	1

Material specifications

Color	orange (RAL 2003)
-------	-------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

SB 3-8-T O. SCHR. - Bridge bar



3026845

<https://www.phoenixcontact.com/us/products/3026845>

Classifications

ETIM

ETIM 8.0	EC000489
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SB 3-8-T O. SCHR. - Bridge bar

3026845

<https://www.phoenixcontact.com/us/products/3026845>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com