

KZMP-RV 8:A-H - Pair of marking masks



3191327

<https://www.phoenixcontact.com/us/products/3191327>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Pair of marking masks, Card, white, labeled, horizontal: Upper case letters, mounting type: adhesive, for terminal block width: 7.62 mm, Number of individual labels: 20



Commercial data

Item number	3191327
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BE19
Product key	BE1ZWX
GTIN	4017918093488
Weight per piece (including packing)	12.69 g
Weight per piece (excluding packing)	11.93 g
Customs tariff number	39269097
Country of origin	CH

KZMP-RV 8:A-H - Pair of marking masks



3191327

<https://www.phoenixcontact.com/us/products/3191327>

Technical data

Product properties

Product type	Labeled terminal marker
Pitch	7.62 mm

Marking

Number of individual labels	20
Number of individual labels per row	1
Printing direction	horizontal
Printing	Upper case letters

Mounting

Mounting type	adhesive
---------------	----------

Material specifications

Color	white
-------	-------

Dimensions

Width	65 mm
Pitch	7.62 mm
Length	7.61 mm

KZMP-RV 8:A-H - Pair of marking masks



3191327

<https://www.phoenixcontact.com/us/products/3191327>

Classifications

UNSPSC

UNSPSC 21.0	39121410
-------------	----------

KZMP-RV 8:A-H - Pair of marking masks



3191327
<https://www.phoenixcontact.com/us/products/3191327>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com