

BN-ZB 6,2/WH-100:UNBEDRUCKT - Marker pin Zack strip



5060867
<https://www.phoenixcontact.com/us/products/5060867>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker pin Zack strip, Strip, white, unmarked, can be labeled with: CMS-P1-PLOTTER, mounting type: plug in, Number of individual labels: 1000, text field height: 4 mm, text field width: 4 mm

Commercial data

Item number	5060867
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BG05
Product key	BG2112
GTIN	4017918096090
Weight per piece (including packing)	0.297 g
Weight per piece (excluding packing)	0.26 g
Customs tariff number	39269097
Country of origin	PL

BN-ZB 6,2/WH-100:UNBEDRUCKT - Marker pin Zack strip



5060867

<https://www.phoenixcontact.com/us/products/5060867>

Technical data

Notes

General	Can be labeled with CMS
---------	-------------------------

Product properties

Product type	Klemmenmarker
--------------	---------------

Marking

Number of individual labels	1000
Number of individual labels per row	10
Identification technology	Plotter

Dimensions

Width	4.00 mm
Height	3.97 mm
Depth	5.50 mm

Material specifications

Color	white (RAL 9010)
Flammability rating according to UL 94	V2
Base element material	PA
Components	free from silicone and halogen

Environmental and real-life conditions

UV resistance

Specification	ISO 4892-2:2013-03 (following)
---------------	--------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	plug in
---------------	---------

BN-ZB 6,2/WH-100:UNBEDRUCKT - Marker pin Zack strip



5060867

<https://www.phoenixcontact.com/us/products/5060867>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

BN-ZB 6,2/WH-100:UNBEDRUCKT - Marker pin Zack strip



5060867
<https://www.phoenixcontact.com/us/products/5060867>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.004 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com