

EM-DUO 120/15/GFI/AUX - Socket



5600639

<https://www.phoenixcontact.com/us/products/5600639>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Socket, connection method: Screw connection, color: ivory, nom. voltage: 125 V AC, nominal current: 15 A, standards/specifications: UL 508, UL 943

Commercial data

Item number	5600639
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BE76
Product key	BE7613
GTIN	4046356687973
Weight per piece (including packing)	320.4 g
Weight per piece (excluding packing)	261.4 g
Customs tariff number	85366990
Country of origin	US

EM-DUO 120/15/GFI/AUX - Socket

5600639

<https://www.phoenixcontact.com/us/products/5600639>



Technical data

Product properties

Product type	Socket
For country-specific use in	USA
	Canada
	Mexico
	Bahamas
	Bermuda
	Columbia
	Costa Rica
	Ecuador
	El Salvador
	Panama
	Puerto Rico
	Taiwan
	Venezuela
	Virgin Islands
Response time	25 ms (6 mA)

Connection data

Connection method	Screw connection
Screw thread	M3
Stripping length	8 mm
Conductor cross-section rigid	0.2 mm ² ... 6 mm ²
Cross section AWG	30 ... 10 (converted acc. to IEC)
Conductor cross-section flexible	0.2 mm ² ... 4 mm ²
Nominal current	15 A
Nominal voltage	125 V AC

Dimensions

Width	82 mm
Height	135 mm
Depth	49 mm

Material specifications

Color	ivory
Insulating material	Polycarbonate & ABS blend

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 60 °C

EM-DUO 120/15/GFI/AUX - Socket



5600639

<https://www.phoenixcontact.com/us/products/5600639>

Standards and regulations

Standards

Standards/regulations	UL 508
	UL 943
	CSA 22.2

EM-DUO 120/15/GFI/AUX - Socket



5600639

<https://www.phoenixcontact.com/us/products/5600639>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/5600639>

	 UL Listed Approval ID: E238705			
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	125 V	15 A	30 - 10	30 - 10

	 cUL Listed Approval ID: E238705			
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	125 V	15 A	30 - 10	-

EM-DUO 120/15/GFI/AUX - Socket



5600639

<https://www.phoenixcontact.com/us/products/5600639>

Classifications

ECLASS

ECLASS-13.0	27142305
ECLASS-15.0	27142305

ETIM

ETIM 9.0	EC001663
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

EM-DUO 120/15/GFI/AUX - Socket



5600639

<https://www.phoenixcontact.com/us/products/5600639>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(c), 7(a), 7(c)-I
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com