

Single-Display Gas Spring-Arm Desktop Clamp or Grommet for 13" to 34" Displays - USB and Audio Ports, Aluminum

MODEL NUMBER: DDR1732SAL



Aluminum desk clamp mounts your 13 to 34 in. monitor at a comfortable height to free up valuable space on your desk or work area.

Features

Rugged Aluminum Desk Clamp Lifts Your Monitor Above Your Work Area's Surface

This VESA-compliant desktop clamp mounts a flat- or curved-screen display above your desk, table or workstation, allowing you to free up valuable surface space. Recommended for home or office use, the DDR1732SAL fits most flat- and curved-panel monitors from 13 to 34 inches. The durable aluminum frame tolerates frequent adjustments, and the swiveling aluminum arm supports up to 19.8 pounds (9 kg). Instead of clamping the unit to your desktop, you may install it using the included grommet. All hardware is included. Cable management brackets along the arms prevent excess cord clutter.

Swivel, Tilt and Rotate the Screens to Find the Most Comfortable Viewing Angles

The gas spring arm adjusts independently to optimize viewing angles, minimize glare and improve ergonomics. To minimize screen glare, reduce eye fatigue and increase viewing comfort, the mount features -90° to +90° tilt, -90° to +90° swivel and 90° rotation for positioning your screen. Easy screen adjustment lets you quickly find just the right angle without interrupting your workday.

Connect Your Favorite Devices to Help You Get Through the Workday

The base of the DDR1732SAL features a USB 3.0 port with pass-through charging for connecting a USB mobile device. Two 3.5 mm audio jacks allow connection of a microphone and speakers.

VESA-Compliant Mounting Ensures Display Compatibility

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this monitor stand supports the following VESA mounting hole patterns: 75 x 75 and 100 x 100.

Highlights

- Aluminum frame attaches securely to your desk via clamp or grommet
- -90° to +90° tilt, -90° to +90° swivel and 90° rotation help you find the perfect angle
- Base includes a USB 3.0 port and dual 3.5 mm audio ports for connecting peripherals
- Durable aluminum flex arm blends into any decor and supports up to 19.8 lb.
- VESA compliance ensures compatibility with 75 x 75 and 100 x 100 mounting patterns

System Requirements

Flat- and curved-screen monitors from 13 to 34 in.

Package Includes

- DDR1732SAL Single-Display Flex-Arm Desktop Clamp
- Mounting hardware for clamp and grommet
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332262493



Powering Business Worldwide

TRIPP LITE
SERIES

Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Silver
Material of Construction	Aluminum
VESA Pattern (mm)	75x75; 100x100
Motion	Full
Mounting Location	Desk Clamp; Grommet
Degrees of Motion	-90/+90 for Tilt, Swivel and Rotate
Minimum Screen Size (in.)	13
Minimum Screen Size (cm)	33.02
Maximum Screen Size (in.)	34
Maximum Screen Size (cm)	86.4
Maximum Weight Capacity (lbs.)	19.8
Maximum Weight Capacity (kg)	9
Number of Displays	1
Shipping Dimensions (hwd / in.)	18.30 x 17.60 x 4.40
Shipping Dimensions (hwd / cm)	46.48 x 44.70 x 11.18
Shipping Weight (lbs.)	10.20
Shipping Weight (kg)	4.63
Unit Dimensions (hwd / in.)	32.300 x 24.700 x 4.500
Unit Dimensions (hwd / cm)	82.4 x 62.74 x 11.43
Unit Weight (lbs.)	10.2
Unit Weight (kg)	4.63
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	Yes
Tools Necessary	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; RoHS3; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.