

Heavy-Duty USB-A to Lightning Sync/Charge Cable, MFi Certified - M/M, USB 2.0, 3 ft. (0.91 m)

MODEL NUMBER: M100-003-HD



Heavy-duty short Lightning cable with bulletproof Aramid fiber construction charges and synchronizes your latest-generation Apple iPhone, iPad or iPod using the USB port on your computer. Designed to stand up to rigorous and frequent use.

Description

The M100-003-HD Heavy-Duty USB Sync/Charge Cable connects your latest-generation iPhone, iPad or iPod to the USB-A port on a computer or USB wall charger, so you can charge your Apple device and transfer data. The reversible 8-pin Lightning plug connects in either direction to ensure fast, easy connection every time. This short Lightning cable is constructed using bulletproof Aramid fiber. The cable's enhanced protection stands up to the strain of rigorous and frequent use. The double-braided nylon jacket and integral strain relief provide additional strength and flexibility to endure the stress and abuse of frequent use. The 3-ft. (0.91 m) heavy-duty Lightning cable is MFi-certified for use with the latest generation of iPhone, iPad and iPod devices.

Features

Syncs and Charges Your Apple 8-Pin Electronic Devices Connects to USB-A port on computer or wall charger MFi-certified for use with the latest generation of iPhone, iPad and iPod devices

Reversible Lightning Connector Fumble-free reversible Lightning plug connects in either direction for quick connection every time

Heavy-Duty Construction with Bulletproof Aramid Fiber Cable is designed to stand up to strain of rigorous and frequent use Double-braided nylon jacket helps maintain top performance and long life Integral strain relief helps cable and connectors move freely without stress or cracking

Highlights

- Cable with bulletproof Aramid fiber withstands strain of frequent use
- Connects to USB-A port on computer or wall charger
- MFi-certified for use with iPhone, iPad and iPod devices
- Nylon braiding maintains top performance and long life
- Reversible Lightning plug connects in either direction

Applications

- Charge and sync your Apple iPhone, iPad or iPod using the USB-A port on your computer or a wall charger up to 3 ft. away
- Transfer photos and other important files between an external hard drive and your Apple device

System Requirements

- Computer, laptop or charger with USB-A port
- Most current iPhone, iPad and iPod devices

Package Includes

- M100-003-HD Heavy-Duty USB Sync/Charge Cable with Lightning Connector, 3 ft.

Specifications

OVERVIEW	
UPC Code	037332207302
Technology	Lightning; USB 2.0 (High Speed)
Cable Type	Passive



Powering Business Worldwide

TRIPP LITE
SERIES

INPUT	
Maximum Input Amps	2
POWER	
USB Power Delivery (PD) Charging Support	No
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	LIGHTNING (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
CHARGING	
Total Charging Watts	12
PHYSICAL	
Material of Construction	TPE, PVC, Nylon, Aramid Fiber
Cable Jacket Color	Black; White
Cable Jacket Material	TPE
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.6mm
Wire Gauge (AWG)	30/24
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Shipping Dimensions (hwd / in.)	0.91 x 4.57 x 2.36
Shipping Dimensions (hwd / cm)	2.31 x 11.61 x 5.99
Shipping Weight (lbs.)	0.05
Shipping Weight (kg)	0.02
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Packaging Type	Box
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 176°F (-20° to 80°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing



Powering Business Worldwide

TRIPP LITE
SERIES

Storage Humidity Range	0% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	12W (5V/2.4A)
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
Data Transfer Rate	480 Mbps
Angled Plug	No
STANDARDS & COMPLIANCE	
Product Certifications	MF i
Product Compliance	RoHS; REACH; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.