

Universal USB-A to Lightning, USB Micro-B and USB-C Sync/Charge Cable (M/3xM), MFi Certified, Black, 6 ft. (1.8 m)

MODEL NUMBER: M101-006-LMC-BK



All-in-one cable connects your Apple, Android and Bluetooth mobile devices to the USB-A port on your computer or wall/car charger.

Features

All-in-One USB-A Sync/Charge Cable Connects to All Your Frequently Used Mobile Devices

Now you can charge and sync all your devices with one cable, and avoid the tangle and clutter of multiple cords. This USB-A cable features Apple Lightning, USB Micro-B and USB-C connectors on the same end, which allows you to connect almost any mobile device to your computer, laptop or wall charger's USB port. Not only does the M101-006-LMC-BK charge and power your device, it also syncs and transfers data at USB 2.0 speeds up to 480 Mbps.

Single Cable Solution Offers Flexibility in Meeting Your Syncing and Charging Needs

Ideal for home, office or travel use, this versatile cable is compatible with most smartphones, tablets, digital cameras, Bluetooth headphones and power banks, including your Android LG, Google or Samsung Galaxy phone or Surface Pro tablet. The 20V 3A (60W) Lightning connector is MFi-certified for safe use with the latest generation of iPhone, iPod and iPad devices.

Reversible Connectors Attach in Either Direction

Unlike traditional USB cables that connect in only one direction, the reversible USB-C and 8-pin Lightning connectors plug into a compatible port in either direction for an instant connection every time.

Specifications

OVERVIEW	
UPC Code	037332254856
Technology	Lightning; USB 2.0 (High Speed)
Cable Type	Passive
INPUT	

Highlights

- Single charge/sync cable for all your devices cuts down on clutter-carry just one!
- Compatible with popular Apple, Android and Surface smartphones and tablets
- MFi-certified for broad compatibility with your Apple iPhone, iPad or iPod device
- Supports USB 2.0 speeds up to 480 Mbps to ensure reliable charging and data transfers
- Reversible Lightning and USB-C plugs connect in either direction for no-fuss use

Applications

- Charge and sync your iPhone, iPad, Android smartphone, tablet or other device using the USB port on your computer or a wall charger up to 6 ft. away
- Transfer photos and other important files between an external hard drive and your mobile devices

System Requirements

- Computer, laptop or charger with USB-A port
- Mobile device with Lightning, USB Micro-B or USB-C port
- Most current iPhone, iPad and iPod devices

Package Includes

M101-006-LMC-BK USB-A to Lightning, USB Micro-B and USB-C Sync/Charge Cable (M/3xM), Black, 6 ft. (1.8 m)



Powering Business Worldwide

TRIPP LITE
SERIES

Maximum Input Amps	3
POWER	
USB Power Delivery (PD) Charging Support	No
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	LIGHTNING (MALE)
Side B - Connector 2	USB C (MALE)
Side B - Connector 3	MICRO-USB B (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
CHARGING	
Total Charging Watts	10
PHYSICAL	
Material of Construction	TPE, Nylon
Cable Jacket Color	Black
Cable Jacket Material	TPE
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.7mm
Wire Gauge (AWG)	19/27
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	0.91 x 4.57 x 2.36
Shipping Weight (kg)	0.02
Unit Packaging Type	Box
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 176°F (-20° to 80°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	60W (20V/3A)



Powering Business Worldwide

TRIPP LITE
SERIES

FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
Data Transfer Rate	480 Mbps
Angled Plug	No
STANDARDS & COMPLIANCE	
Product Certifications	MFi
Product Compliance	RoHS; REACH; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.