

USB Sync/Charge Cable with Apple 30-Pin Dock Connector, White, 3 ft. (0.91 m)

MODEL NUMBER: **M110-003-WH**



Charge and sync your Apple 30-pin iPhone, iPad or iPod using the USB port on your computer.

Description

The M110-003-WH USB Sync/Charge Cable connects your iPhone, iPad or iPod with the USB port on any computer, so you can charge your Apple device and transfer data. This 3-ft. (0.91 m) cable is MFi-certified for use with the latest generation of iPhone, iPad and iPod devices.

Features

Syncs and Charges Your Apple 30-Pin Electronic Devices MFi-certified for use with the latest generation of iPhone, iPad and iPod devices)

Compact and Convenient to Use Connects your 30-pin iPhone, iPad or iPod device and the USB port on your computer or wall charger Works with all computers

Highlights

- Features an Apple-compatible 30-pin plug and a USB-A plug
- Works with any computer
- MFi-certified for broad compatibility with your Apple iPhone, iPad or iPod
- Compatible with all Apple devices with 30-pin connectors

System Requirements

- USB-equipped computer or charger
- iPhone, iPad, iPad mini, iPad mini 2, iPad mini 3, iPad mini 4, iPad Air, iPad Air 2, iPad Pro 12.9 inch, iPad Pro 10.5 inch, iPad Pro 9.7 inch and iPod Touch devices with Lightning port

Package Includes

- M110-003-WH USB Sync/Charge Cable with Apple 30-Pin Dock Connector

Specifications

OVERVIEW	
UPC Code	037332190062
Technology	USB 2.0 (High Speed)
Cable Type	Passive
INPUT	
Maximum Input Amps	2
POWER	
USB Power Delivery (PD) Charging Support	No



Powering Business Worldwide

TRIPP LITE
SERIES

CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	30 PIN APPLE (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
CHARGING	
Total Charging Watts	10.5
PHYSICAL	
Material of Construction	PVC
Cable Jacket Color	White
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	2.8mm
Cable Length (ft.)	3
Cable Length (m)	0.91
Shipping Dimensions (hwd / in.)	5.20 x 0.90 x 2.60
Shipping Dimensions (hwd / cm)	13.21 x 2.29 x 6.60
Shipping Weight (lbs.)	0.10
Shipping Weight (kg)	0.05
Unit Packaging Type	Box
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 176°F (-20° to 80°C)
Relative Humidity	0-90% non-condensing
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	10.5W (5V/2.1A)
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
Data Transfer Rate	480 Mbps
Angled Plug	No



Powering Business Worldwide

TRIPP LITE
SERIES

STANDARDS & COMPLIANCE	
Product Certifications	MFi
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.