

VGA to HDMI Active Adapter Cable with Audio and USB Power (M/F), 1080p, 6 in. (15.2 cm)

MODEL NUMBER: **P116-003-HD-U**



Converts analog VGA video and USB 2-channel audio for use with an HDMI projector, monitor or television without having to upgrade your source equipment. Ideal for home audio/video setups, media presentations and digital signs.

Description

The P116-003-HD-U VGA to HDMI Converter Adapter with Audio and USB Power saves you money on costly computer upgrades by converting a VGA video signal for viewing on an HDMI projector, monitor or television. You can display a rich high-definition signal in your home audio/video setups, media presentations or digital signage using your tried-and-true analog source equipment. The unit is ready to use right from the box with no software or drivers to install. It's powered via the built-in USB cable, so no external power supply is required.

Connect the built-in VGA cable to your computer's VGA port and the built-in USB cable to your computer's USB port. Then, use an HDMI cable (such as the P568-Series) to connect the P116-003-HD-U to your HDMI display. The LED will indicate when the unit is properly connected and when it is transmitting video. In addition to high-definition video resolutions up to 1080p, the unit supports 24-bit True Color (8 bits per channel) and video transfer rates of 6.75 Gbps (1.65 Gbps per channel). Small enough to carry in your pocket, backpack or laptop bag, the P116-003-HD-U works with all operating systems. When connected to a Windows computer, it also supports USB audio along with the HDMI video signal.

Features

Converts Video from VGA to HDMI Ideal for home audio/video setups, media presentations and digital signs
Supports HD video resolutions up to 1080p
Supports video transfer rates up to 6.75 Gbps (1.65 Gbps per channel)
Supports 24-bit True Color (8 bits per channel)
Supports USB audio signals (Windows computers only)
Convenient LED lights red to indicate connection, blue to indicate video transmission

Plug-and-Play Convenience Ready to use right from the box—no software or drivers required
Connects easily to source's VGA and USB ports and display's HDMI port
Powered via USB—no external power supply required
Eliminates the need for costly equipment upgrades
Works with all operating systems
Easy to carry in pocket, backpack or laptop bag

Highlights

- Supports high-definition video resolutions up to 1080p
- Supports video transfer rates up to 6.75 Gbps
- Supports 24-bit True Color (8 bits per channel)
- No external power supply required
- Plug and play—no software or drivers to install

System Requirements

- Source with VGA video port and USB port
- Display with HDMI port

Package Includes

- P116-003-HD-U VGA to HDMI Converter Adapter with Audio and USB Power, 1080p
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332189400



Powering Business Worldwide

TRIPP LITE
SERIES

Product Type	Active Cable
Technology	HDMI; VGA/SVGA
VIDEO	
Max Supported Video Resolution	1920 x 1200 (1080p)
CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side A - Connector 2	USB A (MALE)
Side B - Connector 1	HDMI (FEMALE)
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Length (ft.)	3.3
Cable Length (m)	1.01
Cable Length (in.)	39.6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	1.00 x 6.30 x 4.70
Shipping Dimensions (hwd / cm)	2.54 x 16.00 x 11.94
Shipping Weight (lbs.)	0.25
Shipping Weight (kg)	0.11
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty
Product Warranty Period (U.S. & Canada)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.