

3.5 mm Mini Stereo Audio 4-Position TRRS Headset Extension Adapter Cable (M/F), 6 ft. (1.8 m)

MODEL NUMBER: P318-006-MF



Extends the connection distance between your iPhone, mobile phone or computer headset by 6 ft.

Features

- Molded strain-relief prevents the cable from being bent at sharp angles at the TRRS connectors to minimize the stress at the plug termination point
- Provides greater flexibility by enabling you to move more freely, while working at your computer with VOIP applications (Skype, chat programs)
- 4-pole 3.5mm male/female connectors with molded PVC strain relief
- Nickel-plated connectors
- 90% Spiral Wrapped Connector provides shielding against EMI and RFI interference
- Length: 2 meters (6 ft)

Specifications

OVERVIEW	
UPC Code	037332184597
Product Type	Passive Cable
Technology	Stereo Audio
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	3.5MM, 4-POSITION (FEMALE)
Side B - Connector 1	3.5MM (MALE)
Latching or Gripping Connector	No

Highlights

- 6-ft, 3.5mm 4-position TRRS Headset Extension Cable
- Fully-molded for a lifetime of use

System Requirements

- Headset and equipment with 4-position TRRS 3.5mm connections

Package Includes

- 3.5mm Mini Stereo Audio 4 Position TRRS Headset Extension Cable (M/F) 6-ft.



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.07
Shipping Weight (kg)	0.03
FEATURES & SPECIFICATIONS	
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.