

HDMI to VGA + Audio Active Adapter Cable (HDMI to Low-Profile HD15 + 3.5 mm M/M), 6 ft. (1.8 m), TAA

MODEL NUMBER: P566-006-VGA-A



Converts an HDMI audio/video signal for presentation on an existing VGA monitor, projector or television and 3.5 mm mini stereo speakers, saving you the time, effort and expense of upgrading to a new HDMI display.

Features

Send High-Definition HDMI Audio/Video Signals to a VGA Display

- Connects HDMI source to a VGA monitor, projector or TV
- Ideal for displaying video on large monitor or digital sign
- Low-profile HD15 connector fits neatly into tight spaces
- Attached 3.5 mm plug allows connection of compatible mini stereo speakers
- Plug-and-play—no software or drivers necessary

Vibrant, Superior Video Quality

- Supports HD video resolutions up to 1920 x 1200 @ 60 Hz

Superior Materials for Superior Performance

- Foil and braid shielding for reliable protection from EMI/RFI line noise
- Gold-plated HDMI connector and contacts for maximum conductivity and minimum data loss
- Integral strain relief reduces stress and adds flexibility
- Impedance-matched twisted-pair construction reduces crosstalk and interference
- USB Micro-B port provided in case additional power is needed

Specifications

OVERVIEW

UPC Code

037332201041

Highlights

- Supports HD video resolutions up to 1920 x 1200 @ 60 Hz
- Gold-plated HDMI connector for maximum conductivity
- Foil and braid shielding for reliable EMI/RFI line noise protection
- Low-profile VGA connector fits neatly into tight spaces
- Plug-and-play with no software or drivers required

System Requirements

- Computer or other source with HDMI female connector
- Monitor or other display with VGA female connector
- USB Micro-B to A cable and USB power source (only if additional power is needed)

Package Includes

- P566-006-VGA-A HDMI to VGA + Audio Active Converter Cable, 6 ft.



Powering Business Worldwide

TRIPP LITE
SERIES

Product Type	Active Cable
Technology	HDMI; VGA/SVGA
Cable Type	Active
VIDEO	
Max Supported Video Resolution	1920 x 1200 (1080p)
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HD15 (MALE) - LOW PROFILE
Side B - Connector 2	3.5MM (MALE)
Side B - Connector 3	MICRO-USB B (FEMALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.00
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 22.86
Shipping Weight (lbs.)	0.40
Shipping Weight (kg)	0.18
FEATURES & SPECIFICATIONS	
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.