

Slim High-Speed HDMI Cable with Ethernet and Digital Video with Audio, UHD 4K 60 Hz (M/M), White, 10 ft. (3.1 m)

MODEL NUMBER: **P569-010-SLIM-W**



HDMI cable with special slim design connects audio/video components to a 4K display in your home theater or digital signage application.

Features

Connects 4K Audio/Video Equipment in Digital Signage and Home Theater Applications

This high-speed HDMI cable securely connects laptops, tablets, PCs, Blu-ray players, game consoles, Roku/Apple TV boxes, satellite/cable TV receivers and other devices with HDMI outputs to HDTVs, HD monitors, projectors or home theater receivers with HDMI inputs. The 4K P569-010-SLIM-W is backward compatible with all your existing HDMI devices and will transmit 1080p signals.

Special Slim Design for Better Airflow and Easier Installation

The P569-010-SLIM-W is smaller in diameter than standard HDMI cables. This increases airflow in tight spaces, which helps keep your equipment cool and properly functioning. It also cuts down on clutter in crowded racks, home theaters and patch panels, and makes the cable easier to install around corners and through cable management panels.

Transmits 4K Video with 4:4:4 Color

The P569-010-SLIM-W supports Ultra HD 4K resolutions up to 4096 x 2160 at 60 Hz and uncompressed 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor.

Premium Construction for Superior Performance

This rugged HDMI cable features premium foil and braid shielding that ensures reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data. Corrosion-resistant gold-plated connectors and contacts provide maximum conductivity and minimum data loss to guarantee a clear transmission free of interference. Integral strain relief gives the cable extra flexibility, reduces stress and helps the cable move freely without cracking or breaking loose from the connector.

Highlights

- Supports UHD resolutions up to 4K @ 60 Hz (4:4:4) for heightened video quality
- Special slim design cuts cable clutter and makes it easy to route through tight spaces
- Foil/braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Plug-and-play operation with no software required for easy, immediate installation

Package Includes

P569-010-SLIM-W Slim High-Speed HDMI Cable, M/M, White, 10 ft. (3.1 m)

Specifications

OVERVIEW

UPC Code

037332290441



Powering Business Worldwide

TRIPP LITE
SERIES

Product Type	Passive Cable
Technology	HDMI
Cable Type	Passive
VIDEO	
Max Supported Video Resolution	3840 x 2160 (4K) @ 60Hz
Max Supported Color Depth	24-bit True Color
HDR Support	No
3D Video Supported	No
Chroma Sub Sampling	4:4:4
EDID Support	Yes
Signal Transmission	Bidirectional
DisplayPort Alt Mode	No
AUDIO	
Audio Specification	Stereo Audio
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HDMI (MALE)
Connector Plating	Gold
Contact Plating	Gold
Connector Style	Straight
Latching or Gripping Connector	No
PHYSICAL	
Color	White
Material of Construction	PVC
Cable Jacket Color	White
Connector Color	White
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.6MM
Wire Gauge (AWG)	36
Cable Length (ft.)	10
Cable Length (m)	3.05
Cable Length (in.)	120



Powering Business Worldwide

TRIPP LITE
SERIES

Minimum Bend Radius	36mm
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.06
Unit Dimensions (hwd / in.)	9.000 x 7.000 x 0.500
ENVIRONMENTAL	
Operating Temperature Range	32° to 133°F (0° to 45°C)
Storage Temperature Range	-40° to 176°F (-40° to 80°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
COMMUNICATIONS	
EDID Compatible	Yes
Consumer Electronics Control (CEC) Supported	No
FEATURES & SPECIFICATIONS	
EMI/RFI Line Noise Protection	No
Integrated/Removable Cable	No
MST Support	No
Antibacterial	No
Fully Molded Connector Ends	No
Ohms	No
Integral Strain Relief	No
Impedance-Matched Twisted-Pair Construction	No
Scaler Function	No
IP67 Rated	No
Armored Cable	No
HDCP Specification	1.4
Driver Required	No
DIN Mountable	No
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.