



Powering Business Worldwide

TRIPP LITE
SERIES

DisplayPort 1.2 to VGA Active Adapter Cable (DP with Latches to HD15 M/M), 10 ft. (3.1 m), TAA

MODEL NUMBER: P581-010-VGA-V2

Converts a DisplayPort v1.2 video signal for display on a VGA monitor, projector or television.

Features

Send High-Quality DisplayPort v1.2 Video Signals to a VGA Display

- Connects DisplayPort computer to VGA-enabled monitor, projector or TV
- Ideal for displaying video on large monitor or digital sign
- Low-profile VGA connector fits neatly into available space; no jamming between wall and monitor or impeding neighboring connections
- HD15 and latching DisplayPort male connectors
- No separate adapter required

Vibrant, Superior Video Quality

- Supports computer video resolutions up to 1920 x 1200
- Supports HD video resolutions up to 1920 x 1080 (1080p)
- Converts Single-Mode and Dual-Mode (DP++) DisplayPort output
- Perfect for use with graphics cards, such as AMD Eyefinity, that do not output DP++ signals

Superior Materials for Superior Performance

- Double shielding with foil and braid for maximum EMI/RFI protection
- Nickel-plated connectors with gold-plated contacts for excellent conductivity
- Latching DisplayPort plug for secure connection
- Integral strain relief for long life

Highlights

- Active adapter cable for use with any Displayport port
- Low-profile VGA connector fits neatly into available space; no jamming between wall and monitor or impeding neighboring connections
- Supports computer video resolutions up to 1920 x 1200
- Supports HD video resolutions up to 1920 x 1080 (1080p)
- No separate adapter required
- Nickel-plated connectors with gold-plated contacts

Package Includes

- P581-010-VGA-V2 DisplayPort 1.2 to VGA Active Adapter Cable, 10 ft.

Specifications

OVERVIEW	
UPC Code	037332191946
Product Type	Active Cable
Technology	VGA/SVGA; DisplayPort
Cable Type	Active
VIDEO	
Max Supported Video Resolution	1920 x 1200 (1080p)
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	HD15 (MALE)
Latching or Gripping Connector	Yes



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Length (ft.)	10
Cable Length (m)	3.05
Cable Length (in.)	120
Shipping Dimensions (hwd / in.)	10.00 x 8.00 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 20.32 x 1.27
Shipping Weight (lbs.)	0.44
Shipping Weight (kg)	0.20
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
IP68 Rated	No
Displayport Specification	1.2
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.