

UPS Replacement Battery Cartridge for select APC UPS

MODEL NUMBER: RBC7A



Highlights

- Up to 30% longer runtime than basic replacements
- OEM certified premium batteries
- Rugged, leakproof construction
- Maintenance-free
- Wide operating temperature range

Package Includes

- UPS battery replacement cartridge
- Instruction manual with installation, recycling and warranty information

Description

These premium UPS replacement battery cartridges breathe new life into UPS systems suffering from expired or weak internal batteries. Each replacement battery set is carefully configured to meet or exceed all of the original manufacturer specifications and ships pre-assembled and ready for installation into your UPS system. Reusable packaging holds expired batteries for recycling center delivery. Compatible with select UPS systems from most major brands. See the UPS replacement battery page to confirm compatibility and quantity required.

Features

- Restores your UPS to its original runtime specifications
- Comes pre-assembled and ready for installation into your UPS system
- Reusable packaging holds expired batteries for recycling center delivery
- Compatible with many brands and models, including APC models SU700XL, SU700XLNET, SU1000XLNET, BP1400, SUVS1400, SU1400, SU1400NET, and SUA1500

Specifications

OVERVIEW	
UPC Code	037332118431
BATTERY	
Included Battery Set	Contains (2) 12V 17AH sealed lead acid batteries
Typical Battery Lifespan	3 - 5 years, depending on host UPS operating conditions
PHYSICAL	
Shipping Dimensions (hwd / in.)	9.25 x 8.75 x 9.25
Shipping Dimensions (hwd / cm)	23.50 x 22.22 x 23.50



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Weight (lbs.)	25.80
Shipping Weight (kg)	11.70
Unit Dimensions (hwd / in.)	6.750 x 6.000 x 7.200
Unit Dimensions (hwd / cm)	16.7 x 14.9 x 17.8
Unit Weight (lbs.)	24.1
Unit Weight (kg)	10.93
ENVIRONMENTAL	
Relative Humidity	0-95% non-condensing
Operating Elevation	0-10000 ft. (0-3000 m)
Storage Elevation (ft.)	0 - 50,000
Storage Elevation (m)	0 - 15,200 m
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.