

Specifications

Photo is representative

Eaton

EGS0774A3200B1000R

Eaton PowerXL DG1 enclosed adjustable frequency drive, 60 hp, Circuit breaker disconnect, 480V, Three-phase, Low overload, 77A output, NEMA 3R, Start-stop pushbutton with speed pot and HOA switch, 480V, No Brake Chopper

General specifications

PRODUCT NAME	Eaton PowerXL DG1 enclosed adjustable frequency drive
CATALOG NUMBER	EGS0774A3200B1000R
UPC	786670008668
PRODUCT LENGTH/DEPTH	21 in
PRODUCT HEIGHT	45 in
PRODUCT WIDTH	21 in
PRODUCT WEIGHT	350 lb
WARRANTY	2 year
COMPLIANCES	Contact Manufacturer
CERTIFICATIONS	Contact Manufacturer

Product specifications

BRAKE CHOPPER	No brake chopper
AMPERAGE RATING	77A output
CONTROL OPTIONS	Start-stop pushbutton with speed pot and HOA switch
HORSEPOWER	60 hp
PHASE	Three-phase
SPECIAL FEATURES	Circuit breaker disconnect
TYPE	Standard
INPUT VOLTAGE	480 V
OUTPUT VOLTAGE	480 V
ENCLOSURE	NEMA 3R
OVERLOAD CURRENT	Low overload

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet -
EGS0774A3200B1000R](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

