

USB 3.0 SuperSpeed to Serial ATA (SATA) and IDE Adapter for 2.5 in. or 3.5 in. Hard Drives

MODEL NUMBER: U338-000



Ideal for home or business applications that require a fast, convenient way to transfer files, add external storage and format hard drives without having to install them.

Description

The U338-000 USB 3.0 to SATA/IDE Adapter provides individual or simultaneous connection to either a Serial ATA or IDE drive (2.5/3.5/5.25") to allow you to configure hard drives without having to install them first. With transfer speeds up to 6 Gbps (w/SATA III), the U338-000 provides a fast, convenient way to format hard drives or transfer files. You can also transfer data between a SATA and IDE drive over the adapter. The unit features both 2.5-inch IDE (44-pin) and 3.5-inch (40-pin) connections and a 22-Pin SATA Data + Power connector. It works with any SATA and certain IDE drives (see compatibility list). Windows-compatible AI-OTB One Touch Backup software is included to allow you to quickly backup and restore files. The U338-000 is compatible with Windows and macOS. Manufactured using top-quality materials to ensure error-free data transmission and hard drive formatting.

Features

- USB 3.0 and below compliant
- SATA III (6 Gbps) and below compliant
- Supports plug-and-play
- USB Mass Storage Class Bulk-Only Transport specification
- 40-pin and 44-pin IDE connectors and a 22-Pin SATA Data + Power connector
- Compatible with 2.5/3.5/5.25" SATA and IDE drives up to 4TB
- Includes AI-OTB One Touch Backup software and button for one-touch backup
- Compatible with Windows and Mac

Specifications

OVERVIEW	
UPC Code	037332174932
Technology	SATA/eSATA

Highlights

- SuperSpeed (5 Gbps)/Hi-Speed (480 Mbps)/Full-Speed (12 Mbps) compliant
- SATA III (6 Gbps)/SATA II (3 Gbps)/SATA I (1.5 Gbps) compliant
- Compatible with 2.5/3.5/5.25" SATA and IDE drives up to 4TB
- Includes AI-OTB One Touch Backup software and button for one-touch backup
- Compatible with Windows and Mac

System Requirements

- 2.5/3.5/5.25" SATA and/or IDE drive up to 4TB
- Computer with an available USB port (USB 3.0 port required to reach maximum speeds)
- AI-OTB software compatible with Windows OS up to 8.1
- U338-000 compatible with Windows and Mac

Product Versions and Backup Software

Package Includes

- USB 3.0 to SATA/IDE Adapter
- USB 3.0 A to Micro-B cable, 2.5 ft.
- 4-pin Molex power cable, 4 in.
- External power supply with NEMA 1-15P plug and 5 ft. cord (Input: 100-240V, 50/60Hz, 0.8A; Output: 12V, 2A)
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

POWER	
AC Adapter	Input: 100-240V, 50/60Hz, 0.8A; Output: 12V, 2A; 5 ft.
CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	22 PIN SATA + POWER (FEMALE)
Side B - Connector 2	40 POS. SOCKET (FEMALE)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	2.90 x 5.40 x 4.70
Shipping Dimensions (hwd / cm)	7.37 x 13.72 x 11.94
Shipping Weight (lbs.)	1.00
Shipping Weight (kg)	0.45
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.