

4-Port USB-C Hub, USB 3.2 Gen 2 (10 Gbps), 4x USB-C Ports, 100W PD Charging, Thunderbolt 3 Compatible, Gray

MODEL NUMBER: U460-004-4C-G2C



Adds 4 new USB-C ports to the USB-C or Thunderbolt 3 port on your MacBook, Chromebook, Windows laptop, PC, tablet or smartphone.

Features

USB-C Hub Connects 4 USB Peripherals to Your Computer's USB-C or Thunderbolt 3 Port

This USB-C hub with PD charging connects up to four USB-C peripherals to your MacBook, Chromebook, Windows laptop, PC, tablet or smartphone. Expand the potential of your device by connecting multiple USB peripherals that can help you do your job faster, easier and better, such as external storage (M.2 SATA or NVMe enclosures), USB-C thumb drives, digital cameras, wireless headsets and other podcasting equipment. An ideal choice for Work From Home and Work From Anywhere professionals, the U460-004-4C-G2C also charges your smartphones, tablets and other mobile devices.

Transfers Data at Lightning-Fast USB 3.2 Gen 2 Speeds

All four USB ports transfer data at speeds up to 10 Gbps, which is double the rate of USB 3.2 Gen 1. The USB ports are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices. Three fast-charging ports provide up to 5V 1.5A (7.5W) for charging smartphones and other mobile devices.

PD Charging Port Charges Host Device via AC Wall Charger

The USB-C Power Delivery port supports power output up to 20V 5A (100W), which is more than sufficient for charging and powering the connected source device, such as a MacBook Pro, Windows laptop or Chromebook, or a handheld gaming device like a Steam Deck, Nintendo Switch or ASUS ROG. Just connect the device's wall charger to both the USB-C PD port and an AC outlet. **Note:** 15W is reserved for powering the hub. User-supplied power adapter and Type-C cable must support 100W charging to reach full charging output of PD charging port.

Ready to Use Right Out of the Package

The plug-and-play USB-C hub requires no software, drivers or external power. The lightweight unit fits easily into a pocket, briefcase or laptop bag for connecting on the go.

Specifications

Highlights

- Travel-sized USB-C hub features 4 USB-C ports for connecting essential peripherals
- All ports support USB 3.2 Gen 2 speeds up to 10 Gbps for fast data transfers
- Power Delivery port supports 20V 5A (100W) power output for charging host device
- 3 ports support 5V 1.5A (7.5W) fast-charging for headsets and other small devices
- Plug-and-play operation with no software required for easy, immediate installation

System Requirements

- Source device with USB-C or Thunderbolt 3 port (USB 3.2 Gen 2 capability required for 10 Gbps speeds)
- Source device's USB-C port must support PD charging to charge the device via the hub's PD charging port

Package Includes

- U460-004-4C-G2C 4-Port USB-C Hub, Gray
- Installation instructions



Powering Business Worldwide

TRIPP LITE
SERIES

UPC Code	037332286109
Product Type	Hub
Device Compatibility	Amazon Kindle; Chromebook; Computer; Headphones; Laptop; Phone; Tablet; Video Game System; Watch
Technology	Thunderbolt; USB 3.x
Country/Region	Global
Host Connector	USB C (MALE)
VIDEO	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DisplayPort Alt Mode	No
DATA	
Data Ports	(4) USB C (FEMALE)
Data Ports Details	(4) USB-C - USB 3.2 Gen 2 (10 Gbps)
INPUT	
Built-In Cable Length (ft.)	0.492
Built-In Cable Length (in.)	5.91
Bus Powered	Yes
BATTERY	
Battery Charging (5V/1.5A Port)	Yes
POWER	
Power Source Type	Bus; USB
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	3.0
CONNECTIONS	
Number of Ports	4
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	(4) USB C (FEMALE)
Connector Plating	Nickel
CHARGING	
Number of Charging Ports	4



Powering Business Worldwide

TRIPP LITE
SERIES

Total Charging Watts	100
Charging Port Type	(4) USB C (FEMALE)
Charging Ports	(1) USB-C: 100W (20V 5A) Power Delivery (PD 3.0); (3) USB-C: 5V 1.5A (7.5W)
Charging Ports / Amps	(3) 1.5A; (1) 5A
Compatible Devices	Chromebook; Laptop; Portable Speaker; Smartphone; Tablet; Video Game Console
PHYSICAL	
Color	Black; Gray
Material of Construction	TPE + ABS
Cable Jacket Color	Black
Cable Jacket Material	TPE
Cable Outer Diameter (OD)	4.3MM
Wire Gauge (AWG)	34/24
Total Number of Ports	4
Shipping Dimensions (hwd / in.)	0.91 x 5.51 x 3.94
Shipping Dimensions (hwd / cm)	2.31 x 14.00 x 10.01
Shipping Weight (lbs.)	0.15
Shipping Weight (kg)	0.07
Unit Dimensions (hwd / in.)	0.470 x 1.570 x 3.780
Unit Packaging Type	Box
Unit Weight (lbs.)	0.15
Unit Weight (kg)	0.07
ENVIRONMENTAL	
Operating Temperature Range	14° to 113°F (-10° TO 45°C)
Storage Temperature Range	14° to 176°F (-10° to 80°C)
Operating Humidity Range	10% TO 85% RH, NON-CONDESNING
Storage Humidity Range	25% TO 93% RH, NON-CONDESNING
Power Provided to Connected Device(s)	(X3) USB-C DATA PORTS: 12W; (X1) USB-C CHARGING PORT: 100W (20V, 5A; 15W IS DEDICATED TO THE FUNCTIONING OF THE HUB)
FEATURES & SPECIFICATIONS	
Over Current Protection	Y
USB Hub Ports	Yes
Number of USB Hub Ports	4
USB Specification	USB 3.2 Gen 2 (Up to 10 Gbps)
Data Transfer Rate	(4) 10 Gbps
Ethernet Support	No



Powering Business Worldwide

TRIPP LITE
SERIES

UASP Support	No
Auto MDIX Support	No
Full Duplex Support	No
Suspend Mode Support	No
Remote Wakeup Support	No
Driver Required	No
STANDARDS & COMPLIANCE	
TAA Compliant Option	N
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS3; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.