




REV.	DATE	DESCRIPTION
NC	01/28/03	INITIAL RELEASE

3.00 [.118] 1.00 [.039]



RECOMMENDED
CABLE STRIPPING DIM'S



NOTE:

1. CRIMPED CONTACT PIN
HEX CRIMP SIZE .068"

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex					
8	CONTACT PIN	BRASS	GOLD	1		DRAWN	G.R.S.	01/28/03							
7	WASHER	BRASS	NICKEL	1		CHECKED									
6	RING	DELRIN	NATURAL	1		ISSUED				PART DESCRIPTION TNC DIRECT SOLDER PLUG HEX COUPLING NUT (.141 SEMI RIGID CABLE)					
5	RETAINER RING	BRASS	NICKEL	1		SHEET	1 OF 1								
4	GASKET	RUBBER	RED	1							PART NO. 122386HEX				
3	INSULATOR	TEFLON	NATURAL	1											
2	BODY	BRASS	GOLD	1											
1	SHELL	BRASS	NICKEL	1						DWG. NO. 122386HEX.DWG REV. NC SIZE A SCALE NA					
	DESCRIPTION	MATERIAL	FINISH	QTY		CAD FILE C:/122/122386HEX.DWG									