





|        | Dim A      | Dim B      |
|--------|------------|------------|
| 2-6p   | $\pm 0.15$ | $\pm 0.15$ |
| 7-12p  | $\pm 0.25$ | $\pm 0.25$ |
| 13-18p | $\pm 0.30$ | $\pm 0.30$ |
| 19-24p | $\pm 0.40$ | $\pm 0.40$ |



RoHS  
Pb<40,000ppm

0000 Standard @ Logo  
000A Standard ANY Logo  
Any special item by  
customer request,  
please contact sales  
department.

|               |  |                                                 |                   |                                                                                                                                                                                                                   |                                                                                       |         |            |
|---------------|--|-------------------------------------------------|-------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------|------------|
| <b>ANYTEK</b> |  |                                                 |                   | <b>CUSTOMER COPY</b><br>ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD |                                                                                       |         |            |
| TITLE         |  | YI 5.08mm Series 4x2P - 4x24P ( Without cover ) |                   |                                                                                                                                                                                                                   |                                                                                       |         |            |
| PART NO.      |  | Ylxx21x1xxxxG                                   |                   | DWG NO.                                                                                                                                                                                                           |                                                                                       | 8YI0001 |            |
| APPROVED      |  | CHECKED                                         | DESIGNED          | DRAWN                                                                                                                                                                                                             | CUST NO.                                                                              |         | Tolerance  |
|               |  |                                                 | Jacke<br>08/11/21 | Jacke<br>08/11/21                                                                                                                                                                                                 |  |         | X. ±0.50   |
|               |  |                                                 |                   |                                                                                                                                                                                                                   |                                                                                       |         | UNIT: mm   |
|               |  |                                                 |                   |                                                                                                                                                                                                                   | SCALE: 2:1                                                                            |         | X.XX ±0.10 |
|               |  |                                                 |                   |                                                                                                                                                                                                                   | SHEET: 01/01                                                                          |         | X° ±1°     |
|               |  |                                                 |                   |                                                                                                                                                                                                                   | REV.: A1                                                                              |         |            |