



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REV.	DESCRIPTION	REVISIONS	DATE	APPROVED
A	NEW RELEASE		02/July/09	
A1	Added heat shrink tube to the SR RA CONN.		06/Jun/2019	
A2	Correction of the DWG NO		17/Dec/2019	



BNC M

BNC M RA



NOTES:

- 1.CABLE:[20AWG(19/0.18±0.008mm)*1C+AL/MYLAR +BRAID(16*8/0.12±0.008mm)]TINNED COPPER INSULATION:PE OD= 2.95±0.10mm COLOR:TRANSPARENT JACKET:HALF MATTE PVC LOW TOXIC; OD=Ø5.0±0.15mm COLOR:UL813 BLACK
 - MARKING:RG58C/U COAXIAL CABLE 50 OHM RoHS
 - 2.CONNECTOR:BNC Male NICKEL-PLATED
 - 3.CONNECTOR:BNC Male RA NICKEL-PLATED
 - 4.MOLDING SR:45Pa PVC BLACK
 - 5.OPEN/SHORT MISS WIRE TEST 100%
 - 6.CONDUCTOR RESISTANCE ≤36.7Ω/km
 - 7.INSULATION RESISTANCE ≥2MΩ DC300V 0.01Sec
- ALL MATERIALS SHALL ACCORD WITH RoHS STANDARD.

SECTION A-A

LENGTH & P/N Table

LENGTH	P/N
1FT(305±20mm)	CO-058BNCRBNC-001
2FT(610±30mm)	CO-058BNCRBNC-002
3FT(914±30mm)	CO-058BNCRBNC-003
4FT(1219±30mm)	CO-058BNCRBNC-004
5FT(1524±30mm)	CO-058BNCRBNC-005
7.5FT(2286±40mm)	CO-058BNCRBNC-007.5
10FT(3048±40mm)	CO-058BNCRBNC-010

PIN OUT:

CENTER	CENTER
SHELL	SHELL



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:				E&R NO.		Amphenol Cables on Demand 20 VALLEY ST. ENDICOTT, NY 13760			
DIMENALS				APPROVALS	DATE				
X	±X		±X"	LF	02/July/09	RG58C/U BNC M/BNC M RA			
.XX	±.XX			CHECKED	BA				
.XXX	±.XXX			RESP ENG					
THIRD ANGLE PROJECTION				MFG ENG		SIZE	DWG. NO.	REV.	
						A	CO-058BNCRBNC-XXX	A2	

NOTES: UNLESS OTHERWISE SPECIFIED

4

3

2

1

SCALE

SHEET

OF