



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REV.	DESCRIPTION	REVISIONS	DATE	APPROVED
A	NEW RELEASE		08/Aug/2009	
A1	ADD LENGTH 75FT		24/Dec/2009	
A2	ADD LENGTH 202mm & 1.5FT		30/Jan/2018	
A3	ADD LENGTH 50FT.		12/Jun/2019	



LENGTH & P/N Table

LENGTH	P/N
202mm+10/-0mm	CO-174BNCX200-202mm
1FT(305±20mm)	CO-174BNCX200-001
1.5FT(457.2±20mm)	CO-174BNCX200-001.5
2FT(610±30mm)	CO-174BNCX200-002
3FT(914±30mm)	CO-174BNCX200-003
4FT(1219±30mm)	CO-174BNCX200-004
5FT(1524±30mm)	CO-174BNCX200-005
7.5FT(2286±40mm)	CO-174BNCX200-007.5
10FT(3048±40mm)	CO-174BNCX200-010
12FT(3658±50mm)	CO-174BNCX200-012
15FT(4572±50mm)	CO-174BNCX200-015
25FT(7620±100mm)	CO-174BNCX200-025
35FT(10668±100mm)	CO-174BNCX200-035
50FT(15240±100mm)	CO-174BNCX200-050
75FT(22860±100mm)	CO-174BNCX200-075



SECTION A-A

- NOTES:
- CABLE:[26AWG(7/0.16±0.008mm)*1C +BRAID(16*4/0.12±0.008mm)]TINNED COPPER INSULATION:PE OD= 1.52±0.07mm ;COLOR:TRANSPARENT JACKET:HALF MATTE PVC LOW TOXIC;OD=Ø2.54±0.10mm COLOR:UL813 BLACK.
 - MARKING:RG-174/U COAXIAL CABLE RoHS
 - CONNECTOR:BNC Male NICKEL-PLATED
 - MOLDING SR:45Pa PVC BLACK
 - OPEN/SHORT MISS WIRE TEST 100%
 - CONDUCTOR RESISTANCE $\leq$ 150Ω/km
 - INSULATION RESISTANCE $\geq$ 2MΩ DC300V 0.01Sec
- ALL MATERIALS SHALL ACCORD WITH RoHS STANDARD.

PIN OUT:

CENTER	CENTER
SHELL	SHELL



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:		EAR NO.		Amphenol Cables on Demand 20 VALLEY ST. ENDICOTT, NY 13760	
DECIMALS		APPROVALS		DATE	
.X	±.X	LF		08/Aug/2009	
.XX	±.XX	CHECKED		08/Aug/2009	
.XXX	±.XXX	BA			
THIRD ANGLE PROJECTION		RESP ENG			
C/D FILE:		MFG ENG			
SIZE		DWG. NO.		REV.	
A		CO-174BNCX200-XXX		A3	

NOTES: UNLESS OTHERWISE SPECIFIED