

F										
E										
D										
C										
B										
A										

DCD-XXBFMB-QL8001

XX: No. Of Pin

Connector

O-Ring

Clamp Ring

Seal

Sealing Nut

Pin2 Pin3 Pin1
Pin4 Pin6 Pin5(Long)
6P

Pin Assignments
Front View

UNIT:mm

TOLERANCE
.X ±0.25
.XX ±0.1
.XXX ±0.05
ANGLES ±1°

TITLE

XLOK, D-20A+5A, CABLE W/O SR
F, M, FI SCREW IN, PUSH LOCK

SCALE

1:1

SIZE

A4

SHEET

1

OF

1

REV.

C

WC-REV.

A.3

QC: Inspection item

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO

DWG NO

DCD-XXBFMB-QL8001

CUSTOMER

ALTW

DRAWN BY

Ruru

CHECKED BY

Rita

APPROVED BY

Max

DATE

2021-10-21

DATE

2021-10-21

DATE

2021-10-21

Note:

* RoHS Compliant

* Important dimension

* Waterproof rate: IP68, mated 1m/24h

* Connector

Housing: Thermoplastic, Black

Pin-1: Copper Alloy, Gold plated

Pin-2: Copper Alloy, Nickel plated

Nut: Thermoplastic, Black

O-Ring: Rubber, Gray

* Clamp Ring: Thermoplastic, Black

* Sealing Nut: Thermoplastic, Black

* Seal: Rubber, Dark Gray, OD: Ø8.0mm-Ø14.5mm

* One set assembled in one pe bag

82.0(Ref.)

36.4(Ref.)

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.