





XX: No. Of Pin—




Connl.



Conn2.



Pin Assignments
Front View
Connl.



Pin Assignments
Front View
Conn2.

Blue 藍 (22AWG)	5	5	} Resistor
White 白 (22AWG)	4	4	
Black 黑 (22AWG)	3	3	
Red 紅 (22AWG)	2	2	
Green 綠 (22AWG)	1	1	
Wire Color	Conn.1	Conn.2	

Pin Out

- * RoHS Compliant
- *  Important dimension
- * Waterproof rate: IP68, mated 1m/24h
- * Connector
 - Housing: Thermoplastic, Black
 - Pin: Copper alloy, Gold plated
 - Nut: Metal
- * Connector
 - Housing: Thermoplastic, Black
 - Pin: Copper alloy, Gold plated
 - Nut: Metal
 - O-Ring: Rubber, Green
- * Outer mold: Thermoplastic, Blue
- * Resistor: 1/4W, 120ohm±5% Resistance, Molded Inside The Connector
- * Wire Harness: UL1007 22AWG

UNIT: mm

TOLERANCE

± 0.5 mm

TITLE	ACC, NMEA, APVD, 1 ADA W/O CB MF
-------	-------------------------------------

SCALE 3:2	SIZE A4	SHEET 1 OF 1
REV. A	WC-REV. A.6	QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Ruru	2023-04-28
DWG NO	CHECKED BY	DATE
HMC-XXXX00-MF0-1S001	Rita	2023-04-28
CUSTOMER	APPROVED BY	DATE
ALTW	Max	2023-04-28