







REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LE31650227	2016/05/04	Vicky	Update Note
C	C210669	2021/04/29	Vicky	△C X5
D	C220337	2022/03/04	Vicky	△D X1



Recommend Panel Cut-Out

Assembly Instruction




Note:

- * RoHS Compliant
- * △△ Important dimension
- * Waterproof rate: IPX8, unmated 1m/24h
- * Connector
- Housing: Thermoplastic, Black
- Pin: Copper alloy, Silver plated
- Gasket: Rubber, Gray
- Shield: Metal
- * Nut: Metal
- * Washer: Metal
- * Gasket: Rubber, Gray
- * For panel thickness max: 5.0mm
- * Gasket, nut and washer are packed separately in pe bag




LB20-04PMFS-SN8001	29.0		
LB20-05PMFS-SN8001		29.8	
LB20-07PMFS-SN8001		29.8	33.0


Item No. A B C



4P



5P




7P

△C Pin Assignments Front View

△C LB20-XXPMFS-SN8001

XX: No. Of Pin

UNIT:mm



TOLERANCE

.X ±0.25
.XX ±0.1
.XXX ±0.05
ANGLES ±1°

TITLE

O SEN, M20 48H, 10A
RECEPTACLE, M, F, SOLDER

SCALE

1:1

SIZE

A4

SHEET

1

OF

1

REV.

D

WC-REV.

A.1

QC

Inspection item

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO

DWG. NO

△C LB20-XXPMFS-SN8001

CUSTOMER

ALTW

DRAWN BY

Vicky

CHECKED BY

Rita

APPROVED BY

Lisa

DATE

2016-05-04

DATE

2016-05-04

DATE

2016-05-04