










F		2		3	4	5	6	7	8
E	PCB Layout								
D									
C									
B									
A	UNIT:mm TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°	TITLE N SEN, M12 B, SCREW RECEPTACLE, M, M, PCB R	SCALE 3:2 SIZE A4 SHEET 1 OF 1 REV. F WC-REV. A.1 QC: Inspection item	Amphenol LTW 安費諾亮泰企業股份有限公司	ITEM NO DWG NO CUSTOMER	M12B-XXPMMR-SF7003 ALTW	DRAWN BY Yulong_wang CHECKED BY Jinhai APPROVED BY Jerry	DATE 2016-12-11 DATE 2016-12-11 DATE 2016-12-11	W10814-03-M01A2

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
E	C210309	2021/02/26	Ruru	X2
F	C221923	2022/12/06	Na Liu	X3



M12B-XXPMMR-SF7003

XX: No. Of Pin



- Note:  
- * RoHS Compliant
 - *  Important dimension
 - *  Waterproof rate: IP67, mated
 - * Connector
 - Housing: Thermoplastic, Black
 - Pin: Copper alloy, Gold plated
 - O-Ring: Rubber, Black
 -  * Shield: Metal
 -  * Nut: Metal
 - * O-Ring: Rubber, Gray
 - * For panel thickness max: 3.0mm
 -  * For pcb thickness max: 1.6mm
 - * Nut is packed separately in pe bag