




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REV.		DESCRIPTION	REVISIONS	DATE	APPROVED
A		NEW RELEASE		25/02/07	
A1		CHANGE PLUG BOOT TO MOLDED SR		01/03/07	



LENGTH & P/N Table

LENGTH	P/N	Cable Color
3FT ±1 inch	MP-5ERJ45UNNV-003	Violet
5FT ±2 inch	MP-5ERJ45UNNV-005	Violet
7FT ±2 inch	MP-5ERJ45UNNV-007	Violet
10FT ±3 inch	MP-5ERJ45UNNV-010	Violet
14FT ±3 inch	MP-5ERJ45UNNV-014	Violet
25FT ±4 inch	MP-5ERJ45UNNV-025	Violet
50FT ±8 inch	MP-5ERJ45UNNV-050	Violet
75FT ±8 inch	MP-5ERJ45UNNV-075	Violet
100FT ±8 inch	MP-5ERJ45UNNV-100	Violet



PIN OUT: T568B		
PLUG 1	PLUG 2	COLOR
PIN 1	PIN 1	WHITE/ORANGE
PIN 2	PIN 2	ORANGE
PIN 3	PIN 3	WHITE/GREEN
PIN 4	PIN 4	BLUE
PIN 5	PIN 5	WHITE/BLUE
PIN 6	PIN 6	GREEN
PIN 7	PIN 7	WHITE/BROWN
PIN 8	PIN 8	BROWN



UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:

DIMENS	±X	ANGLES	±X°
X	±X		
XX	±XX		
XXX	±XXX		

THIRD ANGLE PROJECTION



EAR NO.

APPROVALS

DATE

LF

01/03/07

BA

01/03/07

RESP ENG

MPG ENG

SIZE

DWG. NO.

MP-5ERJ45UNNV-XXX

REV

A1

SCALE

SHEET

OF