




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REV.	DESCRIPTION	REVISIONS	DATE	APPROVED
A	NEW RELEASE		25/02/07	
A1	CHANGE PLUG BOOT TO MOLDED SR		01/03/07	



LENGTH & P/N Table

LENGTH	P/N	Cable Color
3FT ±1 inch	MP-5ERJ45UNNNW-003	White
5FT ±2 inch	MP-5ERJ45UNNNW-005	White
7FT ±2 inch	MP-5ERJ45UNNNW-007	White
10FT ±3 inch	MP-5ERJ45UNNNW-010	White
14FT ±3 inch	MP-5ERJ45UNNNW-014	White
25FT ±4 inch	MP-5ERJ45UNNNW-025	White
50FT ±8 inch	MP-5ERJ45UNNNW-050	White
75FT ±8 inch	MP-5ERJ45UNNNW-075	White
100FT ±8 inch	MP-5ERJ45UNNNW-100	White



PIN OUT: T568B		
PLUG 1	PLUG 2	COLOR
PIN 1	PIN 1	WHITE/ORANGE
PIN 2	PIN 2	ORANGE
PIN 3	PIN 3	WHITE/GREEN
PIN 4	PIN 4	BLUE
PIN 5	PIN 5	WHITE/BLUE
PIN 6	PIN 6	GREEN
PIN 7	PIN 7	WHITE/BROWN
PIN 8	PIN 8	BROWN



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:		
DECIMALS	ANGLES	
X	±X°	
XX	±XX	
XXX	±XXX	

THIRD ANGLE PROJECTION	
RESP ENG	
WFG ENG	

E&R NO.		DATE	
DRAWN		01/03/07	
CHECKED		01/03/07	
BA			

SIZE		DWG. NO.	
A		MP-5ERJ45UNNNW-XXX	

ASSEMBLY	
AMPHENOL Cables on Demand	

20 VALLEY ST. ENDICOTT, NY 13760	
----------------------------------	--

ASM CBL. RJ45/RJ45 CAT. 5E	
----------------------------	--

4PR PATCH CORDS	
-----------------	--

REV.	
A1	