












SM12A-XXPFFS-SF800I
XX: No. Of Pin

Recommended
Panel Cut-Out



SM12A-03PFFS-SF800I		2.5	
SM12A-04PFFS-SF800I		2.5	
SM12A-05PFFS-SF800I		2.5	
SM12A-06PFFS-SF800I		2.5	
SM12A-08PFFS-SF800I		2.5	
SM12A-10PFFS-SF800I	4.5	2.5	
SM12A-12PFFS-SF800I	4.5	2.5	
SM12A-17PFFS-SF800I	4.5	2.5	6.5
Item No.	A	B	C
	Pin伸出長度		



Pin Assignment Front View

UNIT : mm

TOLERANCE	
.X	± 0.25
.XX	± 0.1
.XXX	± 0.05
ANGLES	$\pm 1^{\circ}$

TITLE	N SEN, M12 A-STAINLESS, SCREW RECEPTACLE, F. F. SOLDER
-------	---

SCALE 3:2	SIZE A4	SHEET 1 OF 1
REV. C	WC-REV. A.1	QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Allen Pan	2021-08-13
DWG NO	CHECKED BY	DATE
SM12A-XXPFFS-SF8001	Sam Ho	2021-08-13
CUSTOMER	APPROVED BY	DATE
ALTW	Fred Lee	2021-08-13

Note:

- * RoHS Compliant
- *  Important dimension
- *  Waterproof rate: IP68, unmated 1m/24h
- *  IP69K, mated
- * Connector
 - Housing: Thermoplastic, Black
 - Pin: Copper alloy, Gold plated
 - O-Ring: Rubber, Green
- * Shield: Metal
- * Nut: Metal
- * O-Ring: Rubber, Black
- * For panel thickness max: 4.5mm
- * Nut is packed separately in pe bag