




RoHS Compliant

REV	SIGN	DATE	DESCRIPTION	APPROVER
A0		2024.08.21	Initial Release	Shao Bo

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

- Material:
- Item (a) Terminal upper body: PA66,
 - Item (b) Terminal bottom body: PA66 ,
 - Item (c) Terminal lever: PA6 ,
 - Item (d) Terminal Contact: Copper alloy
 - Item (e) Spring: Stainless,
- Electrical:
- | | |
|---|---------|
| UL1059 Group B,C | Group D |
| ●Voltage rating: 600 V | 600 V |
| ●Current rating: 20A | 5A |
| ●Wire range: | |
| Solid wire: 24-12AWG | |
| Stranded wire: 24-12AWG | |
| ●Wire strip length: 9-10 mm | |
| ●Operating temperature: -20°C to +105°C | |
| ●Assembling temperature: -5°C to +105°C | |
| ●Safety Approval: | |
| ●Critical dimension: | |

Part No. TQT xx x x xxxx G

Poles _____

02 : 2 Poles

03 : 3 Poles

04 : 4 Poles

05 : 5 Poles

RoHS compliant (lead<4%)

In copper Alloy

0000: "@" Logo (Standard)

Lever Color

1: Orange 橘色 (標準色)

2: Gray 灰色 (標準色)

3: Red 紅色

4: Yellow 黃色

5: Green 綠色

6: Blue 藍色

7: Brown 棕色

8: Black 黑色

9: White 白色

P: Pink 粉紅色

V: Violet 紫色

M: Multiple Color

N = Number of poles

Dim A	(N-1)×5.0+8.6
Dim B	(N-1)×5.0

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	TQT series terminal block				DWG NO.	8TQT0004		
PART NO.	TQTxxxxxxxxxG				CUST NO.			
APPROVED	CHECKED	DESIGNED	DRAWN			Tolerance		
		Shao Bo 2024.08.21	Shao Bo 2024.08.21			UNIT: mm	X.	±0.50
						SCALE: 1:1	X.X	±0.30
						REV.: A0	X.XX	±0.10
							X°	±1°