



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REV.	DESCRIPTION	REVISIONS	DATE	APPROVED
A	NEW RELEASE		3/DEC/2013	



UHF (PL-259) Male nickel plated

UHF (PL-259) Male nickel plated



SECTION A-A

LENGTH & P/N Table

LENGTH	P/N
5FT(1524±30mm)	CO-213UHFMX20-005
10FT(3048±40mm)	CO-213UHFMX20-010
15FT(4572±50mm)	CO-213UHFMX20-015
25FT(7620±100mm)	CO-213UHFMX20-025
50FT(15240±150mm)	CO-213UHFMX20-050
100FT(30480±300mm)	CO-213UHFMX20-100

NOTES:

1. CABLE:[12AWG(7/0.7526±0.02mm)*1C +BRAID(24*9/0.12±0.008mm)] BARE COPPER INSULATION:PE OD= 7.24±0.15mm ;COLOR:TRANSPARENT JACKET:HALF MATTE PVC LOW TOXIC;OD=Ø10.3±0.20mm COLOR:UL813 BLACK.
 - 2.CONNECTOR:UHF (PL-259) Male nickel plated
 - 3.OPEN/SHORT MISS WIRE TEST 100%
 - 4.CONDUCTOR RESISTANCE ≅5.64Ω/km
 - 5.INSULATION RESISTANCE ≅2MΩ DC300V 0.01Sec
- ALL MATERIALS SHALL ACCORD WITH RoHS STANDARD.

PIN OUT:

CENTER	CENTER
SHELL	SHELL



NOTES: UNLESS OTHERWISE SPECIFIED

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:				EAR NO.		DATE		Amphenol Cables on Demand 20 VALLEY ST. ENDICOTT, NY 13760	
DECIMALS	ANGLES	DRAWN	APPROVALS	DATE	DATE	DATE	DATE	DATE	DATE
±.X	±X°	LF	LF	3/DEC/2013	3/DEC/2013	3/DEC/2013	3/DEC/2013	3/DEC/2013	3/DEC/2013
±.XX	±XX°	CHECKED	BA	3/DEC/2013	3/DEC/2013	3/DEC/2013	3/DEC/2013	3/DEC/2013	3/DEC/2013
±.XXX	±XXX°	THIRD ANGLE PROJECTION	RESP ENG	RESP ENG	RESP ENG	RESP ENG	RESP ENG	RESP ENG	RESP ENG
THIRD ANGLE PROJECTION				SIZE		DWG. NO.		REV.	
A				A		CO-213UHFMX20-XXX		A0	