





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

4-40thread(UNC)

4X THUMBSCREW






D-SUB
9PIN Male



D-SUB
9PIN Male

LENGTH




SEC A-A

LENGTH & P/N Table

LENGTH	P/N	Cable Color
2.5FT ±1 inch	CS-DLSLSZH9MM0-002.5	BLACK
2.82FT ±1 inch	CS-DLSLSZH9MM0-002.82	BLACK
5FT ±2 inch	CS-DLSLSZH9MM0-005	BLACK
6.5FT ±2 inch	CS-DLSLSZH9MM0-006.5	BLACK
10FT ±3 inch	CS-DLSLSZH9MM0-010	BLACK
15FT ±3 inch	CS-DLSLSZH9MM0-015	BLACK
25FT ±4 inch	CS-DLSLSZH9MM0-025	BLACK
50FT ±6 inch	CS-DLSLSZH9MM0-050	BLACK
125FT ±8 inch	CS-DLSLSZH9MM0-125	BLACK

packing:



PIN OUT: 1 TO 1		
Male	Male	Color
PIN1	PIN1	Black
PIN2	PIN2	Brown
PIN3	PIN3	Red
PIN4	PIN4	Orange
PIN5	PIN5	Yellow
PIN6	PIN6	Green
PIN7	PIN7	Blue
PIN8	PIN8	Purple
PIN9	PIN9	Gray
SHIELD	SHIELD	Drain Wire



Amphenol Cables on Demand
20 VALLEY ST., ENDCOTT, NY 13760

LSZH Data Cable 9 PIN D-Sub MM

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:				E&R NO.		DATE		REV.	
DIMEN'S	±X	±XX	±XXX	APPROVALS	DATE	APPROVALS	DATE	SIZE	DWG. NO.
X	±X	±XX	±XXX	DRAWN	LF	CHECKED	BA	12/Dec/2019	CS-DLSLSZH9MM0-XXX
XXX	±XXX	±XXX	±XXX	RES'P ENG		DRG ENG			
THIRD ANGLE PROJECTION				SCALE		SHEET		OF	
OLD FILE:				SCALE		SHEET		OF	

NOTES: UNLESS OTHERWISE SPECIFIED

4

3

2

1