







THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-8A0182	2008/10/07	Vincent	Add Notes
C	LEN1740956	2017/04/10	Vicky	Update Logo
D	CI90310	2019/03/11	Ruru	Modify Note




3Pin Male Connector
Male Pin PCB Layout
3Pin 公接頭
PCB 挖孔位置尺寸圖



Pin Assignments
Front View



Recommended
Panel Cut-Out



Note: 
*  Important Dimension
* Waterproof Rate: IP67, Unmated
* Housing: Thermoplastic, Black
* Pin: Copper Alloy, Gold Plated
* Nut: Thermoplastic, Black
* Gasket: Rubber, Black
 * Use Waterproof Cap or Dust Cap
Panel Thickness Max: 3.0mm
 * Use without Waterproof Cap or Dust Cap
Panel Thickness Max: 4.0mm
* Gasket and Nut are packed separately
in PE bags.

UNIT:mm		TITLE Large, Screw in Conn Mating pair. Panel Lock 3Pin M Conn M Pin		Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO DC-03PMMP-LS7002	DRAWN BY Ruru	DATE 2019-03-11
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°		SCALE 1:1	SIZE A4	SHEET 1 OF 1	DWG NO DC-03PMMP-LS7002	CHECKED BY Rita	DATE 2019-03-11	DATE 2019-03-11
REV. D		WC-REV. A.3	 Inspection item		CUSTOMER ALTW	APPROVED BY Max	DATE 2019-03-11	