


















	1	2	3	4	5	6	7	8								
F	FLKC-XXEFS-XCP-XXX															
E					SERIAL NO.											
					KEY POINT ①											
					PIN CONFIGURATION ②											
					SIZE(CONNECTOR)											
D	KEY POINT ①															
	CODE	G	A	B	C	D										
C	GRAPHIC	0° 	30° 	45° 	60° 	95° 										
	PIN CONFIGURATION (Solder Definition) ②															
B	GRAPHIC	 2 PIN	 3 PIN	 4 PIN	 5 PIN	 6 PIN	 7 PIN	 8 PIN	 10 PIN	 14 PIN	 16 PIN					
A	UNIT:mm  TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°		TITLE FLO IK R PANEL CONNECTOR SCALE 1:1 REV. C			SIZE A4 WC-REV. A.1 SHEET 2 OF 2 QC:Inspection item			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO DWG NO FLKC-XXEFS-XCP-XXX CUSTOMER ALTW		DRAWN BY Kea CHECKED BY Wen APPROVED BY Aric		DATE 2025/10/21 2025/10/21 2025/10/21	
	1	2	3	4	5	6	7	8	W10814-03-0001A2							

