













REV.	ECN NO.	DATE	SIGN	DESCRIPTION
F	C221973	2022/12/26	Ruru	 XI
G	C231034	2023/08/09	Ruru	 XI
H	C251212	2025/09/30	Vicky	 XI



MSAS-XXPMS-SF800I
XX: No. Of Pin



MSAS-03PMMS-SF800I		2.5		
MSAS-04PMMS-SF800I		2.5		
MSAS-05PMMS-SF800I		2.5		
MSAS-06PMMS-SF800I		2.5		
MSAS-08PMMS-SF800I		2.5		
MSAS-10PMMS-SF800I	4.5	2.5		
MSAS-12PMMS-SF800I	4.5	2.5		
MSAS-17PMMS-SF800I	4.5	2.5	6.5	
 Item No.	A	B	C	
	Pin伸出長度			



Pin Assignment Front View

Note:

- * RoHS Compliant
- *  Important dimension
- *  Waterproof rate: IP68, unmated 1m/24h
- *  IP69K, mated
- * Connector
 - Housing: Thermoplastic, Black
 - Pin: Copper alloy, Gold plated
- *  Shield: Metal
- *  Nut: Metal
- * O-Ring: Rubber, Black
- * For panel thickness max: 4.5mm
- *  The Nut Is Packed Separately In The Bag

UNIT: mm				TITLE N SEN, M12 A -SHLD, SCREW RECEPTACLE, M, M, SOLDER		Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO		DRAWN BY Vicky		DATE 2025-09-30	
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±0.1		SCALE 1:1		SIZE A4				SHEET 1 OF 1		DWG NO MSAS-XXPMMS-SF8001		CHECKED BY Ruru	
		REV. H		WC-REV. .0		QC: Inspection item		CUSTOMER ALTW		APPROVED BY Rita		DATE 2025-09-30	