




F										
E										
D										
C										
B										
A										

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C201786	2020/11/18	Ruru	 X3
C	C210497	2021/03/31	Ruru	 X2
D	C222007	2022/12/27	Ruru	 X1

Note:  

* RoHS Compliant

*  Important dimension

 * Waterproof rate: IP68, mated 1m/24h IP69K, mated

* Connector:

Housing: Thermoplastic, Black

Pin: Copper alloy, Gold plated

O-Ring: Rubber, Gray

Nut: Metal

Shield: Metal

Outer mold: Thermoplastic, Black

* Cable: UL2517, Shield, 22#*5C+AL/MY+B, OD=5.7mm, PVC Jacket, Black


* Cable length tolerance: 0.5M < L ≤ 1M: +60/-0 mm
1M < L ≤ 3M: +120/-0 mm
3M < L ≤ 5M: +160/-0 mm
5M < L ≤ 10M: ±100 mm
10M < L ≤ 20M: ±200 mm
20M < L ≤ 30M: ±300 mm
30M < L ≤ 99M: ±500 mm

Pin Out

Pin #	Wire	
5	Shield	灰
4	Gray	黑
3	Black	藍
2	Blue	白
1	White	棕
1	Brown	

Pin # Wire

C1 & C2



5P

Pin Assignments Front View

UNIT:mm  

TOLERANCE ± 0.5mm

TITLE ACC, SEN, B Code, DB-ENDED FF 

SCALE 1:1 SIZE A4 SHEET 1 OF 1

REV. D WC-REV. A  Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO

DWG NO  MSBSXXFL-SBSFL-SDXXX

CUSTOMER ALTW

DRAWN BY Brady DATE 2019/01/24

CHECKED BY Eagle DATE 2019/01/24

APPROVED BY Neo DATE 2019/01/24

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.