





REV.	ECN NO.	DATE	SIGN	DESCRIPTION
G	C221973	2022/12/26	Ruru	 XI
H	C231034	2023/08/10	Ruru	 XI
I	C251374	2025/10/27	Vicky	 XI




Recommended
Panel Cut-Out



XX: No. Of Pin—



PCB Layout



Pin Assignment Front View

Note:

- * RoHS Compliant
- *  Important dimension
- *  Waterproof rate: IP68, unmated 1m/24h
- *  IP69K, mated
- * Connector
 - Housing: Thermoplastic, Black
 - Pin: Copper alloy, Gold plated
- *  Shield: Metal
- *  Nut: Metal
- * O-Ring: Rubber, Black
- * For panel thickness max: 4.5mm
- *  The Nut Is Packed Separately In The Bag

UNIT: mm				TITLE N SEN, M12 B -SHLD, SCREW RECEPTACLE, M, M, PCB S 			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO		DRAWN BY Vicky		DATE 2025-10-27		
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°									SCALE 3:2		SIZE A4		SHEET 1 OF 1		DWG NO  MSBS-XXPMMP-SF8002
				REV. 1				WC-REV. A.5		QC: Inspection item		CUSTOMER ALTW		APPROVED BY Rita	