




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
F	C220799	2022/05/25	Vicky	△F*1
G	C230022	2023/01/07	Zhi Cheng	△G*2
H	C231529	2023/12/08	Lavy	△H*2

△G △F Note:

- * RoHS Compliant
- * ⌀ Important dimension
- * Waterproof rate: IP67, mated
- * Connector Housing: Thermoplastic, Black, RJ45 jack, shielded
- * Nut: Thermoplastic, Black
- * Gasket: Rubber, Gray
- * Use with waterproof cap or dust cap
Panel thickness max: 3.0mm
- * Use without waterproof cap or dust cap
Panel thickness max: 4.2mm
- * Gasket and nut are assembled on connectors
- * Wire: UL1015, 20AWG, Green

UNIT: mm		TITLE	
TOLERANCE		RJ, C PLASTIC, C5E SHLD	
.X	±0.25	FRONT FASTENED, F, PNL JACK S, 3LOCK	
.XX	±0.1	SCALE	1:1
.XXX	±0.05	SIZE	A4
ANGLES	±1°	SHEET	1 OF 1
REV.	H	WC-REV.	B.4
		QC: Inspection item	

Amphenol LTW		ITEM NO	RCP-5SPFFH-TCM7002	DRAWN BY	Lavy	DATE	2023-12-08
安費諾亮泰企業股份有限公司		DWG NO	RCP-5SPFFH-TCM7002	CHECKED BY	Jerry	DATE	2023-12-08
		CUSTOMER	ALTW	APPROVED BY	Fred	DATE	2023-12-08

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.