

REV.

ECN NO.

DATE

SIGN

DESCRIPTION

B

C

D

LEN13B0165~68

C230520

C241128

2013/08/10

2023/04/24

2024/10/08

Cary

Vicky

Vicky

Change Logo To Amphenol

X5

X1

Conn.

5P

Pin Assignments Front View

5	Green	綠	Green	綠
4	Black	黑	Black	黑
3	Blue	藍	Blue	藍
2	White	白	White	白
1	Brown	棕	Brown	棕
	A		B	
Conn.	Wire Color			
	Pin Out			

UNIT:mm

TOLERANCE

±0.5mm

SI-XX0000-K00-YSBXX

XX: No. Of Pin

XX:01~99Meters

01:01Meter

02:02Meters

...

99:99Meters

Amphenol

Logo in both sides

兩面 Logo

Note:

* RoHS Compliant

* Important dimension

* Waterproof rate: IP68, mated 1m/24h

* Connector

Housing: Thermoplastic, Black

Pin: Copper alloy, Gold plated

Nut: Metal

Outer mold: Thermoplastic, Black

* Cable: Nonul, 22AWG*5C+FP, Black, PU Jacket, OD=5.0mm

* Cable length tolerance: 1M: +50/-0 mm

1M < L ≤ 3M: +100/-0 mm

3M < L ≤ 5M: +150/-0 mm

5M < L ≤ 10M: ±100 mm

10M < L ≤ 20M: ±200 mm

20M < L ≤ 30M: ±300 mm

30M < L ≤ 99M: ±500 mm

ACC, SEN, A Code, Y ADA W/ CB

M

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO

DWG NO

CUSTOMER

ALTW

DRAWN BY

CHECKED BY

APPROVED BY

Vicky

Rita

Fred

DATE

DATE

DATE

2024-10-08

2024-10-08

2024-10-08

1

2

3

4

5

6

7

8

W10814-03-0001A2