



Figure similar

Lampholder, Wedge base W2 x 4.6 d, with incandescent lamp 24 V, with holder

product brand name	SIRIUS
product designation	lampholder
product type designation	3SB2
Contact block/ lampholder	
socket design	W2 x 4.6d
number of lampholders	1
General technical data	
product function EMERGENCY STOP function	No
product component	
• diode	No
• lamp transformer	No
• light source	Yes
• series resistor	No
suitability for integration	front element
protection class IP	
• of the enclosure	IP00
• of the terminal	IP00
vibration resistance according to IEC 60068-2-6	20 ... 200 Hz: 5g
reference code according to IEC 81346-2	P
Substance Prohibitance (Date)	07/01/2006
Weight	0.009 kg
operating voltage	
• at AC	
— at 50 Hz rated value	5 ... 60 V
— at 60 Hz rated value	5 ... 60 V
• at DC rated value	5 ... 60 V
Supply voltage	
type of voltage of the supply voltage of the light source	AC/DC
supply voltage of the light source at AC	
• at 50 Hz rated value	24 V
• at 60 Hz rated value	24 V
supply voltage 1 of the light source at DC rated value	24 V
relative negative tolerance of the supply voltage	-15 %
relative positive tolerance of the supply voltage	10 %
Auxiliary circuit	
number of NC contacts for auxiliary contacts	0
number of NO contacts for auxiliary contacts	0
number of CO contacts for auxiliary contacts	0
operational current at DC-13	

- at 24 V rated value

3 A

Connections/ Terminals

type of electrical connection tab terminals

Lamp

type of light source filament lamp

color of the light source clear

Ambient conditions

ambient temperature

- during operation -25 ... +60 °C
- during storage -40 ... +80 °C

Installation/ mounting/ dimensions

fastening method front plate mounting

height 19 mm

width 19 mm

depth 46 mm

Approvals Certificates

General Product Approval



other

Environment

[Confirmation](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SB2304-2H>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SB2304-2H>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SB2304-2H>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SB2304-2H&lang=en

last modified:

4/2/2025