



SIMATIC ET 200SP, BusAdapter: BA SCRJ/FC, media converter FOC-CU 1x SCRJ FO connection and, 1x FastConnect (FC) connection

General information			
Product type designation	BA SCRJ/FC		
HW functional status	from FS04		
Interfaces			
Number of PROFINET interfaces	1; 2 ports (switch) SCRJ/FC		
Supports protocol for PROFINET IO			
• Number of FC (FastConnect) connections	1		
• Number of SCRJ ports	1		
Cable length			
— PCF	100 m		
— Plastic FOC (POF)	50 m		
— Cu conductors	100 m		
Ambient conditions			
Ambient temperature during operation			
• horizontal installation, min.	-25 °C		
• horizontal installation, max.	60 °C		
• vertical installation, min.	-25 °C		
• vertical installation, max.	50 °C		
Altitude during operation relating to sea level			
• Installation altitude above sea level, max.	5 000 m; restrictions for installation altitudes > 2 000 m, see ET 200SP system manual		
Dimensions			
Width	20 mm		
Height	69.5 mm		
Depth	59 mm		
Weights			
Weight, approx.	50 g		
Classifications			
		Version	Classification
	eClass	14	27-24-26-92
	eClass	12	27-24-26-92
	eClass	9.1	27-24-26-92
	eClass	9	27-24-26-92
	eClass	8	27-24-26-92
	eClass	7.1	27-24-26-92
	eClass	6	27-24-26-92
	ETIM	9	EC002584
ETIM	8	EC002584	

ETIM	7	EC002584
IDEA	4	3552
UNSPSC	15	32-15-17-03

Approvals / Certificates

General Product Approval



[Manufacturer Declaration](#)



[KC](#)



For use in hazardous locations



[FM](#)

[CCC-Ex](#)



[Miscellaneous](#)

Maritime application



[NK / Nippon Kaiji Kyokai](#)



Maritime application

Environment



[CCS \(China Classification Society\)](#)



last modified:

4/7/2025